## SIEMENS

## Data sheet

## 6XV1875-5VH10

product type designation product description

## antenna connection cable QMA / N-Connect plug/socket

Connecting cable for SIMATIC NET antennas, preassembled

QMA/ N-Connect male/female Flexible connection cable pre-assembled, for Suitable for railway applications; Flexible adapter cable from antenna with QMA socket to antenna connection cable; length: 1 m.



suitability for use	Adapter cable for connecting an antenna with QMA connection to the flexible connecting cables, suitable for railway applications
wire length	1 m
electrical data	
number of electrical connections	2
type of electrical connection	QMA/N-Connect male/female
transmission frequency	0 6000 MHz
attenuation factor per length	
• at 2.4 GHz / typical	0.47 dB/m
• at 5.2 GHz / typical	0.77 dB/m
● at 5.85 GHz / typical	0.83 dB/m
impedance	
<ul> <li>rated value</li> </ul>	50 Ω
capacity per length / at 1 kHz	80.2 pF/m
relative speed	83 %
mechanical data	
outer diameter	
<ul> <li>of inner conductor</li> </ul>	1.4 mm
of dielectric	3.8 mm
<ul> <li>of cable sheath</li> </ul>	5.5 mm
symmetrical tolerance of the outer diameter / of cable sheath	0.1 mm
material	
<ul> <li>of inner conductor</li> </ul>	Cu, silver plated
of dielectric	SPEX
<ul> <li>of cable sheath</li> </ul>	RADOX
color	
<ul> <li>of cable sheath</li> </ul>	Black
bending radius	
<ul> <li>with single bend / minimum permissible</li> </ul>	25 mm
with multiple bends / minimum permissible	90 mm
number of bending cycles	50
weight per length	47.8 kg/km
ambient conditions	
ambient temperature	
during operation	-30 +100 °C
during storage	-30 +100 °C
during transport	-30 +100 °C

protection class IP	IP67; when plugged in
product features, product functions, product components / general	
product feature	
halogen-free	Yes
silicon-free	Yes
standards, specifications, approvals	
certificate of suitability	fire protection according to DIN 5510-2, NF F 16-101
RoHS conformity	Yes
<ul> <li>fire protection in accordance with EN 45545-2</li> </ul>	Yes
standard	
<ul> <li>for fire behavior / smoke emission</li> </ul>	EN 61034-2
<ul> <li>for fire behavior / flame resistance</li> </ul>	EN 60332-1-2, IEC 60332-3-22, EN 50305,9.1.2
<ul> <li>for fire behavior / toxic gas emission</li> </ul>	NF-X 70-100
reference code	
<ul> <li>according to IEC 81346-2</li> </ul>	WG
<ul> <li>according to IEC 81346-2:2019</li> </ul>	WGB
further information / internet-Links	
Internet-Link	
<ul> <li>to web page: selection aid TIA Selection Tool</li> </ul>	http://www.siemens.com/tia-selection-tool
<ul> <li>to website: Industrial communication</li> </ul>	http://www.siemens.com/simatic-net
<ul> <li>to website: Industry Mall</li> </ul>	https://mall.industry.siemens.com
<ul> <li>to website: Information and Download Center</li> </ul>	http://www.siemens.com/industry/infocenter
<ul> <li>to website: Selection guide for cables and connectors</li> </ul>	https://sie.ag/2QdlxcP
<ul> <li>to website: Image database</li> </ul>	http://automation.siemens.com/bilddb
<ul> <li>to website: CAx-Download-Manager</li> </ul>	http://www.siemens.com/cax
<ul> <li>to website: Industry Online Support</li> </ul>	https://support.industry.siemens.com
last modified.	

last modified:

7/7/2022 🖸