## Ratings

Voltage: 300 V Temperature: -80~200 °C Flammability: VW-1 Oil resistant: 60°C

≥50% elongation and tensile strength after aging

## Conductor

Conductor count: 1
Gauge: 24AWG 0.22 mm²
Material: tinned copper strands
Strand size: Ø0.2mmx7

Resistance at 20 °C: 94.2  $\Omega$  /km max

## Insulator

Material: Fluorinated ethylene propylene (FEP)


Color: yellow

Diameter:  $\emptyset$ 1.26 ± 0.1 Nominal thickness: 0.33 mm Resistance at 20 °C: 2.5 M $\Omega$  /kft min

Wire marking: E339579 UL AWM STYLE 1332 24AWG 200°C 300V VW-1 - - - cUL AWM I A/B 200°C 300V FT1 TENSILITY

## **Mechanical Tests**

After aging at 232±1°C for 7 days
Minimum tensile strength 1.76 kgf/mm2
Minimum elongation 200% original



Revision:	Date:	Description:	Prepared:	Notes:				
Α	5/20/2022	Initial release		RoHS compliant		ENSILITY		
			Verified:  Dimensions are in millimeters. Tolerances: X: ± 0.5 mm X.X: ± 0.3 mm X.XX: ± 0.05 mm	Function test: no open, no short circuit, no intermittent		TENSILITY  tel 1.541.323.3228 800 877.670.7118 fax 1.541.323.4202 web tensility.com		
				Description:	Size: Part number: A 30-02574			
				Wire, hook-up, TS, 24 AWG, UL 1332, 300V, 200C, 1.26 mm, FEP, yellow				
					Scale:	28:1 Sheet 1 of 1		

5 3 2