
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	DIM "A" INCH [mm]	DIM "B" INCH [mm]	DIM "C" INCH [mm]	DIM "D" INCH [mm]	DIM "E" REF. INCH [mm]	DIM "F" REF. INCH [mm]	
SMP12A	0.79 [20.0]	0.79 [20.0]	0.21 [5.4]	0.24 [6.]]	0.55 [14.0]	0.10 [2.6]	
SMP16A	1.00 [25.0]	1.00 [25.0]	0.25 [6.5]	0.30 [7.5]	0.67 [17.0]	0.13 [3.3]	
SMP18A	1.18 [30.0]	1.18 [30.0]	0.28 [7.0]	0.34 [8.7]	0.79 [20.0]	0.18 [4.5]	



В

CUSTOMER

-SIZE

00A

REV

01A 07-30-20

03-10-20

DATE

2

NOTE:

076845

ECN

JBN

02-21-20


BMAG

1

SEE WWW.PANDUIT.COM FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, PART COLOR AND THIRD PARTY RECOGNITION OR COMPLIANCE.

В

А



RELEASED

BMAG

BMAG

СНК

RGB JHAC

APR

JBN

JBN

ΒY

PART NUMBER SEE TABLE TITLE STRONGHOLD MOUNTS ADHESIVE APPLIED CUSTOMER DRAWING ITEM REVISION NAME 00586EBA/01 DATASET FILE NAME 00586EBA_DC/01A THIRD ANGLE PROJECTION 076845 rev.01 MATERIAL DRAWING NUMBER NYLON 6/6 00586EBA_DC DRAWN BY DATE SCALE SIZE СНК А

NONE

SHEET 1 OF 1

2

RGB B. REVISED HOLE DIA TO 0.13 [3.3] WAS 0.138 [3.50]

JHAC A. REVISED HOLE DIA TO 0.10 [2.6] WAS 0.114 [2.90]

DESCRIPTION