



NOTES:

1. MATERIALS AND FINISHES:  
 CONNECTOR A: 112132- BNC STR CRIMP PLUG  
 CONNECTOR B: 112178- BNC R/A CRIMP PLUG  
 CABLE: RG-316
2. ELECTRICAL:  
 A. IMPEDANCE: 50 OHM
3. MECHANICAL:  
 A. TEMPERATURE RANGE: -55° C TO 165° C
4. PACKAGING:  
 A. QUANTITY: SINGLE PACK  
 B. MARKING: BAG TO BE MARKED  
 "AMPHENOL, 95-850-266-XXX, AND DATE CODE"

REVISIONS				
REV	DESCRIPTION	DATE	ECN	BY
A	RELEASE TO MFG.	2/1/2021	15521	DG



LENGTH TABLE		
PART NUMBER (IMPERIAL)	PART NUMBER (METRIC)	LENGTH 'L' IN INCHES [METERS]
95-850-266-006	-	6.000 [0.152]
-	95-850-266M025	9.843 [0.250]
95-850-266-012	-	12.000 [0.305]
95-850-266-016	-	16.000 [0.406]
95-850-266-018	-	18.000 [0.457]
-	95-850-266M050	19.685 [0.500]
95-850-266-024	-	24.000 [0.609]
-	95-850-266M075	29.528 [0.750]
95-850-266-036	-	36.000 [0.914]
-	95-850-266M100	39.970 [1.000]
95-850-266-048	-	48.000 [1.219]

TOLERANCE TABLE	
LENGTH IN INCHES/FT [METERS]	TOLERANCE
0" - 23.90" [0-0.607]	±0.25" [0.006]
24.00" - 59.00" [0.610 - 14.99]	±0.50" [0.013]
5.0' - 24.9' [1.524 - 7.617]	±2.5%
25.0' & UP [7.620 & UP]	±5.0%

DESIGN REQUIREMENTS

- FREQUENCY: DC TO 4.0 GHz     CONTINUITY
- VSWR: ---- :1 MAX     HI-POT: 1500 VRMS
- INS. LOSS: ---- dB MAX     OTHER

**CUSTOMER OUTLINE DRAWING**  
 ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

NOTICE: These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

UNLESS OTHERWISE SPECIFIED  
 DIMENSIONS ARE METRIC [INCHES] AND TOLERANCES ARE:  
 <0.5mm = ±0.05mm    [<0.020 = ±0.002]  
 >0.5 - 6mm = ±0.1mm    [>0.020 - 0.236 = ±0.004]  
 >6.00 - 30mm = ±0.2mm    [>0.236 - 1.181 = ±0.008]  
 >30.00 - 120mm = ±0.3mm    [>1.181 - 4.725 = ±0.012]

MATERIAL

ENGINEER  
D. GEORGE

DATE  
1/31/2021

TITLE  
 BNC STR PLUG TO  
 BNC R/A PLUG  
 RG-316, VARIOUS LENGTHS

SHEET NO. 2 OF 2

SCALE: 1.0:1.0

Amphenol RF

SIZE	DRAWING NO. 95-850-266-XXX	REV
	ITEM NO. 95-850-266-XXX	A
	PART NO. 95-850-266-XXX	

THIRD ANGLE PROJ.    REFERENCE ---    EAR# 10443

ANGLES = ±1°

DATE 1/31/2021

SHEET NO. 2 OF 2    SCALE: 1.0:1.0

REV A