



**Product:** <u>9736</u> ☑

RS232/422 Low Cap, #24-17pr, FPE, Indiv. Foil, PVC Jkt, CM,  $100\Omega$ 

# **Product Description**

Computer EIA RS-232/422, Digital Audio Cable, 17-Pair, 24 AWG stranded (7x32) tinned copper conductors, Datalene® insulation, individually shielded with Beldfoil® (100% coverage) + 24 AWG stranded tinned copper drain wire, overall PVC jacket.

# **Technical Specifications**

## **Product Overview**

Suitable Applications: RS-422 applications; computer communications; low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); digital audio; panel wiring

## **Construction Details**

#### Conductor

Element	Number of Element	Size	Stranding	Material
Pair(s)	17	24 AWG	7x32	TC - Tinned Copper

### Insulation

Element	Material	Nom. Thickness	Color Code			
Pair(s)	PE - Polyethylene (Foam)	0.0185 in (0.470 mm)	0.061 in (1.5 mm)	Black & Red, Black & White, Black & Green, Black & Blue, Black & Yellow, Black & Brown, Black & Orange, Red & White, Red & Green, Red & Blue, Red & Yellow, Red & Brown, Red & Orange, Green & White, Green & Blue, Green & Yellow, Green & Brown		

## Inner Shield

Element	Shield Type	Material	Coverage	Drainwire Type	Notes
Pair(s)	Таре	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC	each pair
Table No	tes:	Isolation Fold (Fo	oil-in)		

# Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.065 in (1.7 mm)	0.671 in (17.0 mm)
Overall Cable Diameter (Nominal):	0.671 in (1	7.0 mm)

## **Electrical Characteristics**

## Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedence	Nom. Velocity of Prop.	Max. Current
Pair(s)	24 Ohm/1000ft (79 Ohm/km)	12.5 pF/ft (41.0 pF/m)	23.2 pF/ft (76.1 pF/m)	100 Ohm	76%	1 Amp per Conductor at 25°C

## Voltage

UL Voltage Rating
300 V (CM), 300 V (UL AWM 2493)

## **Mechanical Characteristics**

## Temperature

UL Temperature	Operating
60°C (UL AWM 2493)	-20°C to +80°C

Max. Pull Tension:	230 lbs (100 kg)
Bulk Cable Weight:	183 lbs/1000ft (272 kg/km)

## **Standards and Compliance**

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	UL1685 UL Loading
NEC / UL Compliance:	Article 800, CM
AWM Compliance:	AWM 2493
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## **Product Notes**

Notes:	Datalene® insulation features include low dielectric constant and a dissipation factor for high-speed, low-distortion data handling. Physical properties include good crush resistance and light weight. Ripcord under jacket.	
--------	--	--

## **History**

Update and Revision: Revision Number: 0.346 Revision Date: 05-05-2023	
---	--

## **Part Numbers**

## Variants

Item #	Color	Putup Type	Length	UPC
9736 060500	Chrome	Reel	500 ft	612825257899
9736 0601000	Chrome	Reel	1,000 ft	612825257882

## © 2023 Belden, Inc

## All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.