

RFEC-3

High quality low loss CFD400 cable suitable for outdoor installation and weather extreme conditions.

Length 5 meter with connectors M-Female to RP-SMA Male



Fully compatible with technologies, products and services by






Features

- ✓ Robust construction for outdoor usage
- ✓ Perfect connector match with RF Explorer high performance antennas and Helium hotspots
- ✓ Very low insertion loss


Specification

	Frequency Range	0-6000MHz
	Length	5 meter ±50mm
	Impedance	50Ω
	VSWR	Typical 1.1 @ 900MHz ≤1.5 max @ 6GHz
	Insertion Loss	Typical 0.9db @ 900MHz ≤2.5dB max @ 6GHz
	Capacitance	76pF/m
	Velocity of Propagation	85%
	Connectors	Type N Male/Jack Type RP SMA Male
	Insulation Resistance	> 1,000 MΩ
	Bend Radius	Min 25.4mm
	Voltage Breakdown	2.5KV
	External Cable Diameter	10.3mm
	Connectors	Type N Female Type RP-SMA Male
	Mating Cycles	> 500
	Jacket Material	PE
	Conductor Material	Copper
	Binder Material	Aluminum/PE Tape
	Braid Material	Tinned copper wire
	Operation Temperature	-30°C to +65°C
	Environmental	RoHS





Insertion Loss



VSWR



5000 ±50 mm 3 All Dimensions in millimeters (mm) 1- RF Connector RP-SMA Male 2- CFD400 cable 10.3mm diameter 3- Heat shrink assembly 13mm diameter 4- RF Connector N Female - Cu Nickel Plated в С D Е Α Conductor Insulation Braid Shield Binder Jacket

Mechanical Specifications