



# Product: <u>8791</u>

Electronic, 3 C #18 Str TC, PVC Ins, OA TC Srv, PVC Jkt

😭 Request Sample

# **Product Description**

Electronic, 3 Conductor 18AWG (7x26) Tinned Copper, PVC Insulation, Overall Tinned Copper Serve Shield, PVC Outer Jacket

# **Technical Specifications**

# Product Overview

Suitable Appli	cations:	low voltage	e analog signa	ls (4-20ma, 0-10v,); lo	w voltage control (24v,	); line level audio; voice communications; panel wiring
Constructi	on Details					
Conductor						
Element	Number of Element	Size	Stranding	Material		
Conductor(s)	3	18 AWG	7x26	TC - Tinned Copper		
nsulation						
Element	Material	Nom	. Thickness	Nom. Insulation Diam	eter Color Code	
Conductor(s)	PVC - Polyvinyl Chlo	ride 0.022	in (0.56 mm)	0.090 in (2.3 mm)	Black, Red, White	
Outer Shield						
Shield Ty	vpe Materia	al C	overage			
Spiral Serve / Screen Tinned Copper (TC) 80%						
Outer Jacket						
Mater	ial Nom. Th	ickness	Nom. Diam	eter		
PVC - Polyvin	yl Chloride 0.028 in (	0.71 mm)	0.260 in (6.60	mm)		
vo roiyiii						

### Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
Conductor(s)	7.06 Ohm/1000ft	47 pF/ft (150 pF/m)	84 pF/ft (280 pF/m)	8 Amps per Conductor at 30°C

#### Voltage

Voltage Rating
450 V

# **Mechanical Characteristics**

#### Temperature

Operating -30°C to +75°C

#### Bend Radius

Stationary Min.Installation Min.2.6 in (66 mm)2.6 in (66 mm)

Max. Pull Tension:	85 lbs (39 kg)
Bulk Cable Weight:	42 lbs/1000ft

# **Standards and Compliance**

Environmental Suitability:	Indoor		
Sustainability:	CA Prop 65		
Flammability / Reaction to Fire:	IEC 60332-1-2		
CPR Compliance:	CPR Euroclass: Eca		
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)		
UK Regulation Compliance:	UKCA Mark		
APAC Compliance:	China RoHS II (GB/T 26572-2011)		

### History

Update and Revision:

Revision Number: 0.503 Revision Date: 01-20-2023

#### **Part Numbers**

#### Variants

ltem #	Color	Putup Type	Length	UPC
8791 060500	Chrome	Reel	500 ft	612825216490
8791 0601000	Chrome	Reel	1,000 ft	612825216483
8791 060U1000	Chrome	UnReel	1,000 ft	612825216476
8791 0605000	Chrome	Reel	5,000 ft	612825216506

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or guality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.