

Computer Power Cord, Right-Angle NEMA 5-15P to C13 - Heavy-Duty, 15A, 125V, 14 AWG, 10 ft. (3.05 m), Black

MODEL NUMBER: **P007-010-15D**











Heavy-duty computer power cord connects a server, PC, monitor or printer to a surge protector, PDU or UPS with a NEMA 5-15R outlet.

Features

5-15P to C13 Power Cable for Network Devices That Require a Heavy-Gauge ConnectionThis computer power supply cable features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. You can use it to connect a computer, server, monitor, laser printer or drive to an AC wall outlet, surge protector, UPS system or PDU. It can also replace or upgrade the standard power cord provided by the device's manufacturer. The 10-ft. (3.05 m) length allows you great flexibility in placing equipment with respect to the power outlet. Note: This cord is not for use in European markets.

Right-Angle PC Power Cable Is Easier to Connect in Tight SpacesThe angled NEMA 5-15P connector makes installations easier in confined spaces, such as the back of a rack enclosure cabinet. When plugged in, the right-angle plug guides the computer power supply cable parallel to the wall, allowing you to push furniture up against a wall to maximize space.

Highlights

- Right-angle 5-15P plug allows easier connection in confined or hard-to-reach spaces
- Recommended for powering larger servers, laser printers and other network devices
- 10-ft. (3.05 m) length allows great flexibility in placing devices in relationship to AC outlet
- Computer power cable replaces or upgrades original manufacturer's power cord
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

Applications

- Connect devices like computers, large servers and laser printers to a PDU up to 10-ft. (3.05 m) away in your data center
- Extend an existing power connection up to 10-ft. (3.05 m) to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer
- Power a device located in a hard-to-access area behind a desk or flush against a wall

Package Includes

 P007-010-15D Heavy-Duty Desktop Computer Power Cord, Right-Angle 5-15P to C13, 10-ft. (3.05 m), Black

Specifications

| OVERVIEW | /IEW | |
|-----------------------------|---|--|
| UPC Code | 037332241856 | |
| Device Compatibility | Computer; Monitor/HDTV; Printer; Server; UPS; PDU | |
| Country/Region | North America | |
| | | |
| INPUT | | |
| Maximum Input Amps | 15 | |
| Voltage Compatibility (VAC) | 125 | |



| PHYSICAL | | |
|---------------------------------|-----------------------------|--|
| Plug Color | Black | |
| Cable Jacket Color | Black | |
| Cable Jacket Material | PVC | |
| Cable Jacket Rating | FT2 | |
| Power Cord Jacket Type | SJT | |
| Cable Outer Diameter (OD) | 9.2mm | |
| Number of Conductors | 3 | |
| Wire Gauge (AWG) | 14 | |
| Wire Gauge (OD - mm²) | 2.08 | |
| Cable Length (ft.) | 10 | |
| Cable Length (m) | 3.05 | |
| Shipping Dimensions (hwd / in.) | 14.17 x 11.80 x 0.50 | |
| Shipping Weight (kg) | 0.35 | |
| ENVIRONMENTAL | | |
| Operating Temperature Range | -4° to 140°F (-20° to 60°C) | |
| Storage Temperature Range | -4° to 140°F (-20° to 60°C) | |
| Operating Humidity Range | 20% to 80% RH | |
| Storage Humidity Range | 20% to 80% RH | |
| CONNECTIONS | | |
| Side A - Connector 1 | NEMA 5-15P - RIGHT ANGLE | |
| Side B - Connector 1 | IEC-320-C13 | |
| FEATURES & SPECIFICATIONS | | |
| Antibacterial | No | |
| Angled Plug | Yes | |
| High Voltage | Yes | |
| Locking Plug | No | |
| Coiled Power Cord | No | |
| STANDARDS & COMPLIANCE | | |
| Product Certifications | cUL Listed; UL Listed | |
| Product Compliance | RoHS | |



| ARRANTY & SUPPORT | |
|-------------------------------------|---------------------------|
| Product Warranty Period (Worldwide) | Lifetime limited warranty |



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.