SIEMENS

Data sheet 6XV1871-5BN20

product type designation

product description

IE Connecting Cable IE FC RJ45-180 / IE FC RJ45-180

Flexible plug-in cable (4-core), preferred length, preassembled with two IE FC RJ45 connectors 2x2

IE connecting cable IE FC RJ45 Plug-180/IE FC RJ45 Plug-180; IE FC Trailing Cable GP Pre-assembled with 2x IE FC RJ45 plug 180; length 20



suitability for use	For connecting Industrial Ethernet stations with an RJ45 interface (10/100 Mbps)
wire length	20 m
electrical data	
number of electrical connections	2
attenuation factor per length	
• at 10 MHz / maximum	0.06 dB/m
• at 100 MHz / maximum	0.2 dB/m
impedance	
• at 1 MHz 100 MHz	100 Ω
relative symmetrical tolerance	
of the characteristic impedance at 1 MHz 100 MHz	5 %
near-end crosstalk per length	
● at 1 MHz 100 MHz	0.5 dB/m
transfer impedance per length / at 10 MHz	20 mΩ/m
loop resistance per length / maximum	120 mΩ/m
operating voltage	
RMS value	80 V
NVP value in percent	66 %
mechanical data	
number of electrical cores	4
design of the shield	Overlapped aluminum-clad foil, sheathed in a braided screen of tin- plated copper wires
core diameter	
of AWG22 insulated conductor	0.75 mm
outer diameter	
 of inner conductor 	0.75 mm
 of the wire insulation 	1.5 mm
 of the inner sheath of the cable 	3.9 mm
of cable sheath	6.5 mm
symmetrical tolerance of the outer diameter / of cable sheath	0.2 mm
material	
 of the wire insulation 	polyethylene (PE)
 of the inner sheath of the cable 	PVC
 of cable sheath 	PVC

color	white trail and have a factor of
of the insulation of data wires	white/yellow/blue/orange
of cable sheath	green
bending radius	20 F mm
with single bend / minimum permissible with multiple bends / minimum permissible	32.5 mm
with multiple bends / minimum permissible with continuous banding.	58.5 mm 100 mm
with continuous bending number of bending cycles	3000000; Drag chain suitable for 3 million bending cycles at a bending
	radius of 100 mm, a speed of 4 m/s and an acceleration of 4 m/s ²
tensile load / maximum	150 N
weight per length	68 kg/km
ambient conditions	
ambient temperature	
during operation	-25 +75 °C
 during storage 	-25 +75 °C
 during transport 	-25 +75 °C
during installation	-10 +60 °C
• note	Electrical properties measured at 20 °C, tests according to DIN VDE 0472
fire behavior	flame resistant according to UL 1685 (CSA FT 4)
chemical resistance	
• to mineral oil	conditional resistance
• to grease	Conditional resistance
• to water	conditional resistance
radiological resistance / to UV radiation	resistant
product features, product functions, product components	s / general
product feature	
halogen-free	No
• silicon-free	Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	Yes; c(ETL)us, CMG FT4 / (ETL)us PLTC / Sun Res / OIL RES
UL/ETL style / 600 V Rating	Yes; cRUus AWM 21694 AWM I A/B 60°C 600V FT2
certificate of suitability	
 EAC approval 	Yes
CE marking	Yes
RoHS conformity	Yes
Marine classification association	
 American Bureau of Shipping Europe Ltd. (ABS) 	No
 French marine classification society (BV) 	No
 Det Norske Veritas (DNV) 	No
Germanische Lloyd (GL)	No
 Lloyds Register of Shipping (LRS) 	No
 Nippon Kaiji Kyokai (NK) 	No
Polski Rejestr Statkow (PRS)	No
reference code	
according to IEC 81346-2	WG
• according to IEC 81346-2:2019	WGB
further information / internet-Links	
Internet-Link	
to web page: selection aid TIA Selection Tool	http://www.siemens.com/tia-selection-tool
to website: Industrial communication	http://www.siemens.com/simatic-net
• to website: Industry Mall	https://mall.industry.siemens.com
 to website: Information and Download Center 	http://www.siemens.com/industry/infocenter
 to website: Selection guide for cables and connectors 	https://sie.ag/2QdlxcP
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAx-Download-Manager	http://www.siemens.com/cax
to website: Industry Online Support	https://support.industry.siemens.com
last modified:	12/31/2021 🖸