

- ★ Green Device Available
- ★ Super Low Gate Charge
- ★ Excellent CdV/dt effect decline
- ★ Advanced high cell density Trench technology

Product Summary





BVDSS	R <sub>DS(on)</sub>	I <sub>D</sub>
20V	17mΩ	6A

Description

The 3416 is the high cell density trenched N-ch MOSFETs, which provide excellent R<sub>DS(on)</sub> and efficiency for most of the small power switching and load switch applications.

The 3416 meet the RoHS and Green Product requirement with full function reliability approved.

SOT23 Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V <sub>DS</sub>	Drain-Source Voltage	20	V
V <sub>GS</sub>	Gate-Source Voltage	±10	V
I <sub>D@TA=25°C</sub>	Continuous Drain Current, V <sub>GS</sub> @ 4.5V <sup>1</sup>	6	A
I <sub>D@TA=70°C</sub>	Continuous Drain Current, V <sub>GS</sub> @ 4.5V <sup>1</sup>	3.3	A
I <sub>DM</sub>	Pulsed Drain Current <sup>2</sup>	20.4	A
P <sub>D@TA=25°C</sub>	Total Power Dissipation <sup>3</sup>	0.9	W
T <sub>STG</sub>	Storage Temperature Range	-55 to 150	°C
T <sub>J</sub>	Operating Junction Temperature Range	-55 to 150	°C

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
R <sub>θJA</sub>	Thermal Resistance Junction-Ambient <sup>1</sup>	---	139	°C/W
R <sub>θJC</sub>	Thermal Resistance Junction-Case <sup>1</sup>	---	---	°C/W

**Electrical Characteristics ( $T_J = 25^\circ\text{C}$  unless otherwise specified)**

Symbol	Parameter	Test condition	Min.	Typ.	Max.	Units
<b>Off Characteristic</b>						
$V_{(BR)DSS}$	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D=250\mu A$	20	-	-	V
$I_{DSS}$	Zero Gate Voltage Drain Current	$V_{DS}=20V, V_{GS}=0V,$	-	-	1	$\mu A$
$I_{GSS}$	Gate to Body Leakage Current	$V_{DS}=0V, V_{GS}=\pm 10V$	-	-	$\pm 10$	$\mu A$
<b>On Characteristics</b>						
$V_{GS(th)}$	Gate Threshold Voltage	$V_{DS}=V_{GS}, I_D=250\mu A$	0.4	0.7	1	V
$R_{DS(on)}$ <small>note2</small>	Static Drain-Source on-Resistance	$V_{GS}=4.5V, I_D=5A$	-	17	22	m $\Omega$
		$V_{GS}=2.5V, I_D=3A$	-	26	36	
<b>Dynamic Characteristics</b>						
$C_{iss}$	Input Capacitance	$V_{DS}=10V, V_{GS}=0V,$ $f=1.0MHz$	-	545	-	pF
$C_{oss}$	Output Capacitance		-	103	-	pF
$C_{rss}$	Reverse Transfer Capacitance		-	90	-	pF
$Q_g$	Total Gate Charge	$V_{DS}=10V, I_D=5A, V_{GS}=4.5V$	-	8	-	nC
$Q_{gs}$	Gate-Source Charge		-	2.5	-	nC
$Q_{gd}$	Gate-Drain("Miller") Charge		-	3	-	nC
<b>Switching Characteristics</b>						
$t_{d(on)}$	Turn-on Delay Time	$V_{DS}=10V, R_L=1.5\Omega,$ $R_{GEN}=3\Omega, V_{GS}=5V$	-	0.5	-	ns
$t_r$	Turn-on Rise Time		-	1	-	ns
$t_{d(off)}$	Turn-off Delay Time		-	12	-	ns
$t_f$	Turn-off Fall Time		-	4	-	ns
<b>Drain-Source Diode Characteristics and Maximum Ratings</b>						
$I_S$	Maximum Continuous Drain to Source Diode Forward Current		-	-	5	A
$I_{SM}$	Maximum Pulsed Drain to Source Diode Forward Current		-	-	20	A
$V_{SD}$	Drain to Source Diode Forward Voltage	$V_{GS}=0V, I_S=5A$	-	-	1.2	V

**Note :**

1. Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature
2. Pulse Test: Pulse Width  $\leq 300\mu s$ , Duty Cycle  $\leq 0.5\%$

Typical Performance Characteristics

Figure 1: Output Characteristics




Figure 2: Typical Transfer Characteristics




Figure 3: On-resistance vs. Drain Current




Figure 4: Body Diode Characteristics




Figure 5: Gate Charge Characteristics





Figure 6: Capacitance Characteristics



Typical Performance Characteristics

Figure 7: Normalized Breakdown Voltage vs. Junction Temperature




Figure 8: Normalized on Resistance vs. Junction Temperature




Figure.9: Maximum Safe Operating Area




Figure.10: Maximum Continuous Drain Current vs. Ambient Temperature






Figure.11: Maximum Effective Transient Thermal Impedance vs. Pulse Width



SOT23 Mechanical tData



DIMENSIONS ( unit : mm )

Symbol	Min	Typ	Max	Symbol	Min	Typ	Max
A	0.9	1.01	1.15	A <sub>1</sub>	0.01	0.05	0.1
b <sub>p</sub>	0.3	0.42	0.5	c	0.08	0.13	0.15
D	2.8	2.92	3	E	1.2	1.33	1.4
e	--	1.9	--	e <sub>1</sub>	--	0.95	--
H <sub>E</sub>	2.25	2.4	2.55	L <sub>p</sub>	0.3	0.42	0.5
Q	0.45	0.49	0.55	v	--	0.2	--
w	--	0.1	--				