

Specification Sheet

Part Number: 156-04007



Robust fir tree design provides low insertion effort yet delivers exceptional retention strength.

Anti-rotational oval fir tree keeps bundle in intended direction.

Heavy duty T120 tie provides 120 lb (534 N) tensile strength to secure bundles up to 4" (104 mm).

Friction tab inside fir tree allows the tie to sit in mount without falling out prior to installation.

3-Pc Cable Tie/Fir Tree Mount, Unassembled Set, 15"L, 12x17mm Hole, PA66HIRHSUV, Black, 500/ctn

Article Number	156-04007
Type	T120R2xDHVSDL12x17
Color	Black (BK)
Quantity Per	carton
Product Description	HellermannTyton's Fir Tree Mounts provide a secure grip in a mounting hole. The mount can slide along the cable tie to adjust orientation as needed. They are optimized for up to 3-to-1 extraction versus insertion force to make assembly fast and easy. These mounts are sold unassembled.
Short Description	3-Pc Cable Tie/Fir Tree Mount, Unassembled Set, 15"L, 12x17mm Hole, PA66HIRHSUV, Black, 500/ctn

Global Part Name

T120R2xDHVSDL12x17-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)

120

Minimum Tensile Strength (Metric)

535

Length L (Imperial)

8.0

Length L (Metric)

203.2

Fixation Method

Fir Tree

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.30

Width W (Metric)

7.6

Bundle Diameter Min (Imperial)

0.20

Bundle Diameter Min (Metric)

5.0

Bundle Diameter Max (Imperial)

4.13

Bundle Diameter Max (Metric)

105.0

Thickness T (Imperial)	0.07
Thickness T (Metric)	1.8
Height H (Imperial)	1.36
Height H (Metric)	34.74
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.26
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.75
Mounting Hole Diameter D (Imperial)	0.47 x 0.67
Mounting Hole Diameter D (Metric)	12.0 x 17.0 mm
Mounting Hole Diameter D Max (Imperial)	0.47 x 0.67
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Material Cable Tie	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Flammability	UL 94 HB

Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)