


## Transient Voltage Suppressor

### Features

- IEC 61000-4-2(ESD) $\pm 20\text{KV}$ (air),  $\pm 15\text{KV}$ (contact)
- IEC61000-4-5(Lightning) 3.0A (8/20 $\mu\text{S}$ )
- IEC61000-4-4(EFT) 40A (5/50nS)
- 60 Watts peak pulse power ( $t_p=8/20\mu\text{S}$ )
- Low capacitance: 0.30pF (Typical)
- Low clamping voltage
- Weight approx. 1.0 mg
- Small package: DFN1006-2L

### Exterior



DFN1006-2L


### Application information

- Serial ATA
- Desktops, Servers and Notebooks
- Cellular Phones
- MDDI Ports
- USB2.0 Data Line Protection
- Display Ports
- HDMI


### Package (top view)



### Agency Approvals

Icon	Description
<b>RoHS</b>	Compliance with 2011/65/EU
<b>HF</b>	Compliance with IEC61249-2-21:2003
	Mean lead free

### Schematic



### Part Number and Electrical Parameter

Part Number	$I_{\text{DRM}}@V_{\text{DRM}}$		$V_{\text{BR}}^{\text{①}}@I_{\text{R}}$		$V_{\text{c}}@I_{\text{pp}}^{\text{②}}$		$V_{\text{c}}@I_{\text{pp}}^{\text{②}}$		$C_{\text{o}}^{\text{③}}$	
	$\mu\text{A}$	V	V	mA	V	A	V	A	pF	
	MAX		MIN		MAX		MAX		TYP	MAX
BV-FA05UCF	0.5	5	6	1	12	1	20	3.0	0.3	0.4

Absolute maximum ratings measured at  $T=25^{\circ}\text{C}$  RH = 45%-75% (unless otherwise noted).

- ① VBR is measured at  $I_{\text{R}}=1\text{mA}$
- ② Surge Waveform: 8/20 $\mu\text{S}$ .
- ③ Off-state capacitance is measured in  $V_{\text{DC}}=0\text{V}$ ,  $V_{\text{RMS}}=0.3\text{V}$ ,  $f=1\text{MHz}$

**Transient Voltage Suppressor**

Part Numbering System

Mark

BV FA 05 U C F  
(1) (2) (3) (4) (5) (6)


- (1) Bencent Transient Voltage Suppressor
- (2) Package:DFN1006-2L
- (3) Off-state Voltage: 5V
- (4) Low Capacitance
- (5) Bidirectional
- (6) Bencent internal code





5T: Part Number

V-I Curve

Parameters	Definition
$V_C$	Clamping voltage
$I_{PP}$	Surge waveform 8/20 $\mu$ s
$V_{DRM}$	Stand-off Voltage
$V_{BR}$	Breakdown Voltage
$I_{DRM}$	Reverse Leakage Current
$I_R$	Test current
$P_{PP}$	Peak Pulse Power Dissipation





Typical Characteristics



Transient Voltage Suppressor

Version: A2 2021-5-17



Thermal Considerations

symbol	Parameter	Value	Unit
T <sub>J</sub>	Operating Junction Temperature Range	-55 to +125	°C
T <sub>S</sub>	Storage Temperature Range	-55 to +150	°C


Environmental Characteristics

Testing items	Technical standards
High temperature Reverse Bias Test	Temperature: 125±3°C Bias=80%V <sub>DRM</sub> Time:168H
High Temperature Life Test	Temperature: 150°C Time:168H
High-low Temperature Cycle test	Temperature: From -40°C to125°C Dwell time : 30min,10~100cycles
High Temperature &High Humidity Test	Temperature: 85°C Humidity:85% Time:168H
Pressure cooker Test	Temperature: 121°C, 2atm. Humidity:100% Time:24H
Resistance of soldering heat	Temperature: 260±5°C Time of dip soldering: 10s, 3times


Note: The above testing items can be specified by customer's special request

**Transient Voltage Suppressor**

Version: A2 2021-5-17

**Product Dimensions**


REF	mm	inch
A	0.32~0.55	0.014~0.022
A1	0.00~0.05	0.000~0.002
A3	0.125REF	0.005REF
D	0.95~1.10	0.037~0.043
E	0.55~0.70	0.022~0.028
L	0.45~0.55	0.018~0.022
e	0.65BSC	0.026BSC
b	0.15~0.35	0.006~0.014


**Recommended Soldering Pad**


REF	mm	inch
A	0.35	0.014
B	0.60	0.024
C	0.35	0.014


## Transient Voltage Suppressor

### Reflow Profile

Reflow Condition		Pb-Free assembly
Pre Heat	Temperature Min	150°C
	Temperature Max	200°C
	Time (min to max)	60 – 180 secs
Average ramp up rate (Liquid)		3°C/s max
Tamp (T <sub>L</sub> ) to peak		3°C/s max
T <sub>S</sub> (max) to T <sub>L</sub> - Ramp-up Rate		3°C/s max
Reflow	- Temperature (T <sub>L</sub> ) (Liquid)	217°C
	- Temperature (T <sub>L</sub> )	60 – 150 secs
Peak Temperature (T <sub>P</sub> )		260±0/-5 °C
Time within 5°C of actual peak Temperature (T <sub>P</sub> )		30secs
Ramp-down Rate		6°C/s max
Time 25°C to peak Temperature (T <sub>P</sub> )		8 mins max.
Do not exceed		260°C



### Package Reel Information



REF	mm	inch
A	0.70+/-0.05	0.028+/-0.002
B	1.15+/-0.05	0.045+/-0.002
d	1.50+0.1/-0	0.059+0.004/-0
D	178.00+/-2.00	7.008+/-0.079
D1	55.00+/-3.00	2.165+/-0.118
D2	13.00+/-0.50	0.512+/-0.020
E	1.75+/-0.10	0.069+/-0.004
F	3.50+/-0.20	0.138+/-0.008
P	2.00+/-0.20	0.079+/-0.008
P0	4.00+/-0.20	0.157+/-0.008
P1	2.00+/-0.20	0.079+/-0.008
W	8.00+/-0.20	0.315+/-0.008
W1	9.50+/-1.00	0.374+/-0.039

OUTLINE	REEL (PCS)	PER CARTON (PCS)	REEL DIAMETERS (mm)	CARTON SIZE(mm)		
				L	W	H
TAPING	10,000	300,000	178	390	370	220