

product type designation

product description

PROFIBUS M12-Cable

Flexible plug-in cable (2-core), preferred length, preassembled with two 5-pole M12 male/female connectors (B-coded)

PROFIBUS M12 plug-in cable (ET 200), Pre-assembled PB FC Trailing Cable with 2 M12 connectors, B-coded, 5-pole; 10 m.



suitability for use

Cable for connecting PROFIBUS stations (e.g. SIMATIC ET 200) to IP 65 degree of protection

cable designation

02YY (ST) C11Y 1x2x0,65/2,56-150 LI KF 40 FR petrol

wire length

10 m

electrical data

number of electrical connections

2

attenuation factor per length

- at 9.6 kHz / maximum 0.003 dB/m
- at 38.4 kHz / maximum 0.004 dB/m
- at 4 MHz / maximum 0.025 dB/m
- at 16 MHz / maximum 0.049 dB/m

impedance

- rated value 150 Ω
- at 9.6 kHz 270 Ω
- at 38.4 kHz 185 Ω
- at 3 MHz ... 20 MHz 150 Ω

relative symmetrical tolerance

- of the characteristic impedance at 9.6 kHz 10 %
- of the characteristic impedance at 38.4 kHz 10 %
- of the characteristic impedance at 3 MHz ... 20 MHz 10 %

loop resistance per length / maximum

133 mΩ/m

shield resistance per length / maximum

14 Ω/km

capacity per length / at 1 kHz

28 pF/m

operating voltage

- RMS value 80 V

mechanical data

number of electrical cores

2

design of the shield

Overlapped aluminum-clad foil, sheathed in a braided screen of tin-plated copper wires

type of electrical connection / FastConnect

Yes

outer diameter

- of inner conductor 0.67 mm
- of the wire insulation 2.56 mm
- of the inner sheath of the cable 5.4 mm
- of cable sheath 8 mm

symmetrical tolerance of the outer diameter / of cable sheath

0.4 mm

material	polyethylene (PE) PVC PUR (TPE-U)
<ul style="list-style-type: none"> of the wire insulation of the inner sheath of the cable of cable sheath 	
color	red/green petrol
<ul style="list-style-type: none"> of the insulation of data wires of cable sheath 	
bending radius	40 mm 120 mm
<ul style="list-style-type: none"> with single bend / minimum permissible with continuous bending 	
number of bending cycles	3000000; Drag chain suitable for 3 million bending cycles at a bending radius of 120 mm (15x D) and an acceleration of 4 m/s ²
tensile load / maximum	100 N
weight per length	77 kg/km
ambient conditions	
ambient temperature	-40 ... +60 °C
<ul style="list-style-type: none"> during operation during storage during transport during installation note 	-40 ... +60 °C -40 ... +60 °C -40 ... +60 °C -40 ... +60 °C Electrical properties measured at 20 °C, tests according to DIN 47250 part 4 respectively DIN VDE 0472
ambient condition / for operation	Limited segment length (see manual for PROFIBUS networks)
fire behavior	flame resistant according to IEC 60332-1-2
chemical resistance	oil resistant according to IEC 60811-2-1 (7x24h/90°C) resistant conditional resistance
<ul style="list-style-type: none"> to mineral oil to grease to water 	
radiological resistance / to UV radiation	resistant
protection class IP	IP65, IP67
product features, product functions, product components / general	
product feature	No Yes
<ul style="list-style-type: none"> halogen-free silicon-free 	
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	Yes; CMX
UL/ETL style / 600 V Rating	No
certificate of suitability	Yes Yes Yes
<ul style="list-style-type: none"> EAC approval CE marking RoHS conformity 	
Marine classification association	No No No No No No No
<ul style="list-style-type: none"> American Bureau of Shipping Europe Ltd. (ABS) French marine classification society (BV) Det Norske Veritas (DNV) Germanische Lloyd (GL) Lloyds Register of Shipping (LRS) Nippon Kaiji Kyokai (NK) Polski Rejestr Statkow (PRS) 	
reference code	WG WGB
<ul style="list-style-type: none"> according to IEC 81346-2 according to IEC 81346-2:2019 	
further information / internet-Links	
Internet-Link	http://www.siemens.com/tia-selection-tool http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter https://sie.ag/2QdlxcP
<ul style="list-style-type: none"> to web page: selection aid TIA Selection Tool to website: Industrial communication to website: Industry Mall to website: Information and Download Center to website: Selection guide for cables and connectors 	

- to website: Image database
- to website: CAx-Download-Manager
- to website: Industry Online Support

<http://automation.siemens.com/bilddb>
<http://www.siemens.com/cax>
<https://support.industry.siemens.com>

last modified:

12/31/2021 