



Product: <u>9745</u>

Electronic, 3 Pr #22 Str TC, PVC Ins, PVC Jkt, CMG

😭 Request Sample

Product Description

Electronic, 3 Pair 22AWG (7x30) Tinned Copper, PVC Insulation, PVC Outer Jacket, CMG

Technical Specifications

Product Overview

onstruction Details onductor lement Number of Element S	low voltage analog signals (4-20m	a, 0-10v,); low voltage d	igital control (24v, …); line level au	dio; computer communication; panel w	
onductor iement Number of Element S	Size Stranding Material				
lement Number of Element S	Size Stranding Material				
lement Number of Element S	Size Stranding Material				
	AWG 7x30 TC - Tinned C				
sulation					
lement Material	Nom. Thickness Nom. Insula	tion Diameter	Color Code		
air(s) PVC - Polyvinyl Chloride	0.011 in (0.28 mm) 0.050 in (1.3	mm) Black & R	ed, Black & White, Black & Green		
iter Jacket					
Material Nom. Th	ickness Nom. Diameter				
VC - Polyvinyl Chloride 0.032 in (0.81 mm) 0.245 in (6.22 mm)				
overall Cable Diameter (Nominal):	0.245 in (6.22 mm)				
leatrical Characteristics					
ectrical Characteristics					
ectricals					
lement Nom. Conductor DCR	Nom. Capacitance Cond-to-Con	d Max. Current			
air(s) 18.2 Ohm/1000ft :	25.5 pF/ft (83.7 pF/m)	1.9 Amps per Conducto	r at 20°C		
ltage					
UL Voltage Rating					
00 V (CMG), 150 V (AWM 2576)					
echanical Characteristic	6				
	5				
mperature					
L Temperature Operating					
0°C -20°C to +80°C					
and Radius					
tationary Min. Installation Min.					
.4 in (61 mm) 2.4 in (61 mm)					
lax. Pull Tension:	55 lbs (25 kg)				
ulk Cable Weight:	32 lbs/1000ft				
tandards and Complianc	0				

Environmental Suitability:	Indoor	
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, FT4, IEC 60332-1-2	
CPR Compliance:	CPR Euroclass: Eca	
NEC / UL Compliance:	Article 800, CMG	
AWM Compliance:	AWM 2576	
CEC / C(UL) Compliance:	CMG	
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)	
UK Regulation Compliance:	UKCA Mark	
APAC Compliance:	China RoHS II (GB/T 26572-2011)	

History

Update and Revision: Revision Number: 0.501 Revision Date: 01-20-2023

Part Numbers

Variants

Item #	Color	UPC
9745 0601000	Chrome	612825258100
9745 060500	Chrome	612825258117
9745 060U1000	Chrome	612825258087
9745 060U500	Chrome	612825258094

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.