# 3M<sup>™</sup> Heat Shrink Tubing VTN-200

# Modified Fluoroelastomer

Data Sheet	September 2019
------------	----------------

Product Description	3M <sup>™</sup> Heat Shrink Tubing VTN-200 is highly abrasion and cut-through resistant and can withstand a wide variety of fuels, lubricants, acids and highly corrosive fluids at temperatures up to 200°C. In addition to its high continuous operating temperature and chemical-resistance properties, this tubing is very flexible and is easily marked by hot-stamp or printwheel methods. When heated in excess of 175°C (347°F), 3M VTN-200 tubing rapidly shrinks to a skintight fit. 3M VTN-200 tubing is rated for continuous operation from −55°C (−67°F) to 200°C (392°F).		
Regulatory Information	For RoHS and REACH information, please visit www.3M.com/regs		
Typical Applications	Because of its excellent high temperature fluid performance, 3M VTN-200 tubing is often used to protect wiring and component covers in aircraft/aerospace applications including electronic control systems and hydraulic fluid transport mechanisms and in chemical plants.		
Shrink Ratio	3M VTN-200 tubing has a 2:1 shrink ratio. When freely recovered, the tubing will shrink to 50% of its as-supplied internal diameter. The recovered wall thickness is proportional to the degree of recovery.		
Standard Color	Black		
Availability	Standard Packaging Spools		
	Order 3M Heat Shrink Tubing VTN-200 by product name, size equivalent to the expanded inside diameter, package type and color. Always order the largest size that will shrink snugly over the component to be covered. Example: VTN-200, 3/16", black, spools.		
	Please contact your local distributor; available from 3M.com/oem [Where to Buy] or call 1-800-676-8381.		



### 3M™ Heat Shrink Tubing VTN-200

## Standard Sizes and Dimensions

Ordering Size	Expanded I.D. (Minimum) In. (mm)	Recovered I.D. (Maximum) In. (mm)	Recovered Wall Thickness (Nominal) In. (mm)
1/8	.125 (3,18)	.062 (1,57)	.030 (0,76)
3/16	.187 (4,75)	.093 (2,36)	.035 (0,89)
1/4	.250 (6,35)	.125 (3,18)	.035 (0,89)
3/8	.375 (9,53)	.187 (4,75)	.035 (0,89)
1/2	.500 (12,70)	.250 (6,35)	.035 (0,89)
5/8	.625 (15,88)	.312 (7,92)	.042 (1,07)
3/4	.750 (19,05)	.375 (9,53)	.042 (1,07)
7/8	.875 (22,23)	.438 (11,11)	.049 (1,24)
1	1.000 (25,40)	.500 (12,70)	.049 (1,24)
1-1/4	1.250 (31,75)	.625 (15,88)	.055 (1,40)
1-1/2	1.500 (38,10)	.750 (19,05)	.055 (1,40)
2	2.000 (50,80)	1.000 (25,40)	.065 (1,65)

#### **Typical Properties**

Technical information provided consists of typical product data and should not be used for specification purposes. Unless otherwise noted, all tests are performed at room temperature.

Application Specifications: AS23053/13\*

<sup>\*</sup>Formerly MIL-I-23053/13, MIL-DTL-23053/13 and SAE-AMS-DTL-23053/13

Physical Property	Typical Value US units (metric)
Tensile Strength	2400 PSI
Ultimate Elongation	450%
Longitudinal Change	+1, -10%
Specific Gravity	1.7
Operating Temperature Range	-55°C to +200°C
Shrink Temperature	175°C
(Min.)	(347°F)
Low Temperature Flexibility 4 hrs @ -55°C	No cracking
Flammability	Self-extinguish
Electrical Property	Typical Value US units (metric)
Dielectric Strength	500 V/mil
Volume Resistivity	10 <sup>12</sup> ohm/cm
Chemical Property  Typical Value US units (metric)	
Corrosion Resistance	Non-corrosive
Fuel & Oil Resistance	Excellent
Solvent Resistance	Excellent
Abrasion Resistance	Excellent
Acids & Alkalis Resistance	Excellent

### 3M™ Heat Shrink Tubing VTN-200

Shelf Life & Storage

3M™ Heat Shrink Tubing VTN-200 has a 5-year shelf life from date of manufacture when stored in a humidity controlled storage (10°C/50°F to 27°C/80°F and <75% relative humidity).

#### 3M is a trademark of 3M Company.

Important Notice	All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product, which are not contained in 3M's current publications, or any contrary statements contained on your purchase order, shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.
Warranty; Limited Remedy; Limited Liability	This product will be free from defects in material and manufacture at the time of purchase. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any direct, indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.



Electrical Markets Division Austin, TX Phone: 800.676.8381 www.3M.com/oem

Please Recycle. Printed in USA. © 3M 2019. All Rights Reserved. 78-9237-1405-5 Rev B