

# Up/Down-Angle Cat6 Gigabit Molded Slim UTP Ethernet Cable (RJ45 Up-Angle M to RJ45 Down-Angle M), Blue, 10 ft. (3.05 m)

MODEL NUMBER: N204-S10-BL-UD











Cat6 cable connects Gigabit Ethernet network components like routers, servers and switches in highdensity data centers.

#### **Features**

**Up-** and Down-Angle Cat6 Ethernet Cable Connects Equipment in Data Centers and VoIP **Networks**This Cat6 cable is ideal for connecting network components, such as printers, computers, copiers, routers, servers, modems and switches, in hard-to-reach areas of space-constrained high-density data centers. Designed for fast transmission and excellent signal quality, this RJ45 patch cable ensures data transfer speeds up to 1 Gbps throughout your Gigabit Ethernet or VoIP network.

Special Slim Design for Better Airflow and Easier Installation in Crowded RacksThis Cat6 UTP patch cord is more than 38% smaller in diameter than standard Cat6a cable. This increases airflow in tight spaces, which helps keep your equipment cool and properly functioning. It also cuts down on clutter in crowded racks and patch panels, and makes the cable easier to install around corners and through cable management panels.

**Up-** and **Down-Angle RJ45 Patch Cable Makes Connecting and Disconnecting Easier**Both RJ45 male connectors are designed at 90-degree angles: one upward, the other downward. This helps prevent excessive bending and reduces stress on the cable. This space-saving cable is easy to plug into patch panels, switches and other devices located in a confined area or behind a desk.

Blue Jacket to Avoid Misidentification That Can Cause Costly Downtime This up/down-angle Cat6 Ethernet cable features a blue PVC jacket and molded blue ends. The blue color allows easy, fast identification in a crowded rack or workstation and helps prevent the cable from becoming inadvertently disconnected.

### **Highlights**

- Cat6 Ethernet patch cable delivers fast transmission speeds up to 1 Gbps in your I AN
- Up-angle and down-angle RJ45 ends are easy to plug into devices pressed against a wall
- Over 38% slimmer than standard Cat6 cables to increase airflow in full racks
- Easy to route around corners and through crowded cable management panels
- Cable is blue for fast, easy identification in a crowded rack or workstation

#### **Applications**

- Build a Gigabit Ethernet or VoIP network through the connection of routers, modems, switches and servers in a high-density data center
- Connect a workstation computer to the company server to gain access to printers, scanners and conjers
- Combine with other Tripp Lite patch cables to set up a colorcoded system in a crowded rack
- Create a connection in a tight space, such as a repurposed server room or behind furniture

#### **Package Includes**

 N204-S10-BL-UD Up/Down-Angle Cat6 Gigabit Molded Slim UTP Patch Cable (M/M), Blue, 10 ft.

## **Specifications**

OVERVIEW	
UPC Code	037332252494



Cat6	
Blue	
PVC	
СМ	
UTP	
4.0 mm	
4 Pair	
Stranded Copper	
28 AWG	
10	
3.05	
120	
304	
9.00 x 7.00 x 0.50	
22.86 x 17.78 x 1.27	
0.07	
14° to 122°F (-10° to 50°C)	
5° to 140°F (-15° to 60°C)	
0% to 90% RH, Non-Condensing	
0% to 90% RH, Non-Condensing	
0% to 90% RH, Non-Condensing	
COMMUNICATIONS	
250 MHz	
500 MHz	
1 Gbps (Gigabit)	
802.3an	
CONNECTIONS	
RJ45 (MALE) - DOWN ANGLE	
RJ45 (MALE) - UP ANGLE	
No	
Gold	



Molded		
EIA/TIA 568B		
Yes		
FEATURES & SPECIFICATIONS		
No		
No		
No		
STANDARDS & COMPLIANCE		
UL Listed; cUL Listed		
CE (Europe); RoHS; IEEE 802.3an 10GBase-T; REACH; UKCA		
WARRANTY & SUPPORT		
Lifetime limited warranty		



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.