## **SIEMENS**

Data sheet 6XV1870-3QN35

## product type designation

product description



## IE TP Cord RJ45/RJ45, 4x2

Patch cable, preferred length, preassembled with two RJ45 connectors (10/100/1000/10000MB)

Industrial Ethernet TP Cord RJ45/RJ45, CAT 6A, TP cable 4x2, preassembled with 2 RJ45 connectors, length  $35\ m.$ 

| suitability for use  | Easy connection of terminal devices to the IE FC cabling system                            |
|--|--|
| cable designation  | LI 02YSCH 4x2x0,15 PIMF GN FRNC  |
| wire length  | 35 m   |
| electrical data  |  |
| number of electrical connections   | 2  |
| attenuation factor per length  |  |
| • at 10 MHz / maximum  | 0.086 dB/m   |
| <ul><li>at 100 MHz / maximum</li></ul>                                   | 0.28 dB/m  |
| <ul><li>at 300 MHz / maximum</li></ul>                                   | 0.501 dB/m   |
| • at 600 MHz / maximum   | 0.735 dB/m   |
| impedance  |  |
| ● at 1 MHz 100 MHz   | 100 Ω  |
| ● at 10 MHz 600 MHz  | 100 Ω  |
| relative symmetrical tolerance   |  |
| <ul> <li>of the characteristic impedance at 1 MHz 100<br/>MHz</li> </ul> | 15 %   |
| <ul> <li>of the characteristic impedance at 10 MHz 600 MHz</li> </ul>    | 10 %   |
| transfer impedance per length / at 10 MHz                                | 10 mΩ/m  |
| loop resistance per length / maximum                                     | 290 mΩ/m   |
| operating voltage  |  |
| RMS value  | 80 V   |
| NVP value in percent   | 80 %   |
| mechanical data  |  |
| number of electrical cores   | 8  |
| design of the shield   | Overlapped aluminum-clad foil, sheathed in a braided screen of tin-<br>plated copper wires |
| core diameter  |  |
| of AWG26 insulated conductor   | 0.5 mm   |
| outer diameter   |  |
| <ul><li>of inner conductor</li></ul>                                     | 0.5 mm   |
| <ul> <li>of the wire insulation</li> </ul>                               | 1 mm   |
| of cable sheath  | 6.2 mm   |
| symmetrical tolerance of the outer diameter / of cable sheath            | 0.3 mm   |
| material   |  |
| of the wire insulation   | polyethylene (PE)  |

| of cable sheath   | FRNC   |
|---|--|
| color   |  |
| <ul> <li>of the insulation of data wires</li> </ul>                       | white/blue, white/orange, white/green, white/brown                               |
| of cable sheath   | green  |
| bending radius  |  |
| <ul><li>with single bend / minimum permissible</li></ul>                  | 31 mm  |
| <ul><li>with multiple bends / minimum permissible</li></ul>               | 43.5 mm  |
| weight per length   | 50 kg/km   |
| ambient conditions  |  |
| ambient temperature   |  |
| during operation  | -25 +80 °C   |
| during storage  | -25 +80 °C   |
| during transport  | -25 +80 °C   |
| during installation   | -25 +80 °C   |
| • note  | In fixed installation -40 °C to 80 °C  |
| fire behavior   | flame resistant according to IEC 60332-1-2, smoke density according to IEC 61034 |
| class of burning behaviour / according to EN 13501-6                      | Eca  |
| chemical resistance   |  |
| • to mineral oil  | oil resistant according to IEC 60811-2-1 (4 h / 70°C)                            |
| • to grease   | Conditional resistance   |
| radiological resistance / to UV radiation                                 | not resistant  |
| protection class IP   | IP20   |
| product features, product functions, product components                   | / general  |
| product feature   |  |
| <ul><li>halogen-free</li></ul>  | Yes  |
| • silicon-free  | Yes  |
| standards, specifications, approvals                                      |  |
| UL/ETL listing / 300 V Rating   | No   |
| UL/ETL style / 600 V Rating   | Yes; E130266 AWM STYLE 21279   |
| certificate of suitability  |  |
| <ul> <li>EAC approval</li> </ul>  | Yes  |
| UL approval   | Yes  |
| RoHS conformity   | Yes  |
| standard for structured cabling   | Cat6A  |
| Marine classification association   |  |
| <ul> <li>American Bureau of Shipping Europe Ltd. (ABS)</li> </ul>         | No   |
| <ul> <li>French marine classification society (BV)</li> </ul>             | No   |
| <ul><li>Det Norske Veritas (DNV)</li></ul>                                | No   |
| Germanische Lloyd (GL)  | No   |
| <ul> <li>Lloyds Register of Shipping (LRS)</li> </ul>                     | No   |
| <ul> <li>Nippon Kaiji Kyokai (NK)</li> </ul>                              | No   |
| Polski Rejestr Statkow (PRS)  | No   |
| reference code  |  |
| • according to IEC 81346-2  | WG   |
| • according to IEC 81346-2:2019   | WGB  |
| further information / internet-Links                                      |  |
| Internet-Link   |  |
| <ul> <li>to web page: selection aid TIA Selection Tool</li> </ul>         | http://www.siemens.com/tia-selection-tool  |
| to website: Industrial communication                                      | http://www.siemens.com/simatic-net   |
| to website: Industry Mall   | https://mall.industry.siemens.com  |
| to website: Information and Download Center                               | http://www.siemens.com/industry/infocenter                                       |
| <ul> <li>to website: Selection guide for cables and connectors</li> </ul> | https://sie.ag/2QdlxcP   |
| • to website: Image database  | http://automation.siemens.com/bilddb   |
| <ul><li>to website: CAx-Download-Manager</li></ul>                        | http://www.siemens.com/cax   |
| <ul> <li>to website: Industry Online Support</li> </ul>                   | https://support.industry.siemens.com   |
| last modified:  | 6/25/2022 🖸  |