



Product: <u>9333</u>

High Perform Instr, 11 Pr #22 Str TC, PVC Ins E2, IS, PVC Jkt, PLTC

😭 Request Sample

Product Description

High Performance Instrumentation, 11 Pair 22AWG (7x30) Tinned Copper, PVC Insulation E2 Color Code, Individual Beldfoil® Shield, PVC Outer Jacket, PLTC

Technical Specifications

Construction Details

Element	Number of Ele	ement	Size	Stranding	M	aterial	
Pair(s)	11	2	22 AWG	7x30	TC - Tir	nned Copper	
Insulatio	nsulation						
Element	Materi	al	Nom	. Thickness	Nom.	Insulation Diame	ter Color Code
Pair(s)	PVC - Polyviny	l Chlorid	e 0.017	in (0.43 mm	n) 0.062	in (1.6 mm)	Black & Red and Numbered
Inner Shi	əld						
Element	Shield Type		Material	C	overage	Drainwire Type	
Pair(s)	Таре	Bi-Lamir	ate (Alur	m+Poly) 10	0%	22 AWG (7x30) T	0
Outer Shi	eld						
Material							
No Shield							
No Shiel							
No Shiel Outer Jac							
Outer Jac		Nom. T	hicknes	s Nom. Di	ameter	Ripcord	
Outer Jac	:ket					Ripcord Yes	

Electricals

Nom. Conductor DCR	Nom. Inner Shield DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
17.2 Ohm/1000ft	12.3 Ohm/1000ft (40.4 Ohm/km)	26 pF/ft (85 pF/m)	45 pF/ft (150 pF/m)	2.4 Amps per Conductor at 25°C

Voltage

UL Voltage Ratin	ĝ
300 V	

Mechanical Characteristics

Temperature

UL Temperature	Operating
UL: 105°C, AWM 2464: 80°C	-20°C to +105°C

Bend Radius

Stationary Min.	Installation Min.	
5.92 in (150 mm)	5.92 in	

Max. Pull Tension:	300 lbs (140 kg)
Bulk Cable Weight:	160 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance
Flammability / Reaction to Fire:	UL1685 FT4 Loading, FT4, IEEE 1202 FT4
NEC / UL Compliance:	Article 725, Article 727, Article 800
AWM Compliance:	AWM 2464
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Revision Number: 0.432 Revision Date: 12-16-2022

Part Numbers

Update and Revision:

Variants

Item #	Color	UPC
9333 0601000	Chrome	612825231172
9333 060500	Chrome	612825231189

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or guality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulators based on their individual usage of the product.