

2-380936-0 ✓ ACTIVE

AMP

TE Internal #: 2-380936-0

Rectangular Connector Hardware, Grommet, -55 – 85 °C [-67 – 185 °

F]

[View on TE.com >](#)



Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Connector Hardware



Connector Hardware Type: **Grommet**

Operating Temperature Range: -55 – 85 °C [-67 – 185 °F]

## Features

### Body Features

Primary Product Material	Flexible PVC
Primary Product Color	Black

### Mechanical Attachment

Connector Hardware Type	Grommet
-------------------------	---------

### Dimensions

Product Length	14.27 mm[.562 in]
Product Height	12.7 mm[.5 in]

### Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

### Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts

 <p>TE Part # 350524-1 24P STR/REL HSG HNGD V0</p>	 <p>TE Part # 480634-1 20P STR/REL HSG HNGD V0</p>	 <p>TE Part # 480594-1 36P STR/REL HSG HNGD V0</p>
---	---	---

### Customers Also Bought


 <p>TE Part #1571999-6 ADP0404=PIANO DIP SWITCH</p>	 <p>TE Part #350689-1 UMNL SOK 24-18 PTPBR L/P</p>	 <p>TE Part #350430-1 04P UMNL PIN HDR ASSY NATL</p>	 <p>TE Part #172501-1 MIC MARK-2 PLUG HSG 21P</p>
--	---	---	--




TE Part #9-5353015-1  
040 III HD 122POS CAP ASSY H RND




TE Part #178780-1  
040/070 HYBRID CAP ASSY 76P



TE Part #3-1437719-6  
T01-0550-S05-FEMALE PLUG  
CONNECTOR SOLDE



TE Part #2-361329-2  
HST300L-BK/100 C/Tie 300x3.6



TE Part #5174385-5  
CLC CONN. CAP ASSY 76P

## Documents

### Product Drawings

[MR SPLT GROMET .375 DIA BLK LF](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_2-380936-0\\_S.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2-380936-0\\_S.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2-380936-0\\_S.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[SOFT\\_SHELL\\_PIN\\_AND\\_SOCKET\\_CONNECTORS\\_CATALOG](#)

English

### Product Specifications

[Application Specification](#)

English

### Product Environmental Compliance

[MD\\_2-380936-0\\_04212016118\\_dmtec](#)



English

[MD\\_2-380936-0\\_04212016118\\_dmtec](#)

English