SIEMENS

Data sheet 6XV1822-5BH30

product type designation

product description

7/8 inch connecting cable

Plug-in cable (5-core), preferred length, preassembled with two 5-pole 7/8 inch male/female-contact connectors

7/8" plug-in cable for Power supply of the ET 200, pre-assembled cable with 2 7/8" connectors, 5-pole, 3 m.



suitability for use	Power supply of ET 200 modules with 7/8 inch power port to IP 65 degree of protection
cable designation	L-Y11Y-Z 5x1x1.5 GR
wire length	3 m
electrical data	
insulation resistance coefficient	1 GΩ·m
operating voltage / RMS value	600 V
conductor cross section / of the power line	1.5 mm²
continuous current / of the power lines	16 A
mechanical data	
number of electrical cores	5
type of electrical connection	7/8 inch - 180
outer diameter	
 of inner conductor 	1.55 mm
 of the wire insulation 	2.73 mm
of cable sheath	10.5 mm
symmetrical tolerance of the outer diameter / of cable sheath	0.3 mm
design of stranding element	Pairs
conductor class	5
material	
 of the conductor 	CU, blank
 of the wire insulation 	PVC
of cable sheath	PUR
product component / PE connection	Yes
marking / of cores	Color, digits
color	
 of the power line insulation 	black
of cable sheath	gray
bending radius	
with single bend / minimum permissible	27 mm
with multiple bends / minimum permissible	63 mm
with continuous bending	75 mm
number of bending cycles	5000000; For use in cable carriers, for 5 million bending cycles with a bending radius of 75 mm, an acceleration of 4 m/s² and a speed of 180 m/min
tensile load / maximum	500 N

weight per length	149 kg/km	
plug		
type of plug interlock	screwed	
design of plug-in connection	7/8 inch - 180	
connector coding	7/8 inch	
ambient conditions		
ambient temperature		
 during operation 	-40 +80 °C	
 during storage 	-40 +80 °C	
 during transport 	-40 +80 °C	
during installation	-40 +80 °C	
fire behavior	Flame-resistant acc. to IEC 60332-1	
chemical resistance		
• to mineral oil	resistant	
• to grease	resistant	
radiological resistance / to UV radiation	resistant	
protection class IP	IP65 / 67	
product features, product functions, product components / general		
product feature		
halogen-free	No	
• silicon-free	Yes	
standards, specifications, approvals		
UL/ETL listing / 300 V Rating	No	
UL/ETL style / 600 V Rating	Yes	
certificate of suitability		
 EAC approval 	Yes	
 RoHS conformity 	Yes	
further information / internet-Links		
Internet-Link		
 to web page: selection aid TIA Selection Tool 	http://www.siemens.com/tia-selection-tool	
to website: Industrial communication	http://www.siemens.com/simatic-net	
to website: Industry Mall	https://mall.industry.siemens.com	
 to website: Information and Download Center 	http://www.siemens.com/industry/infocenter	
 to website: Selection guide for cables and connectors 	https://sie.ag/2QdlxcP	
to website: Image database	http://automation.siemens.com/bilddb	
to website: CAx-Download-Manager	http://www.siemens.com/cax	
 to website: Industry Online Support 	https://support.industry.siemens.com	

last modified: 5/20/2021 🖸