SIEMENS

Data sheet 6XV1801-5GH20

product type designation

product description

Power Connecting Cable M12-90/M12-90

Flexible plug-i...able outl002

Power connecting cable M12-90/M12-90 for the power supply of the ET200, pre-assembled cable with M12 plug and M12 socket, A-coded, 4 pin 2 m.



Fia	HIEL	3 6	imi	lar
- ry	uli	- 3		I CH

suitability for use	Plug-in cable for connecting 24 V power supply to ET 200 & XP-200 with IP 65/67 degree of protection			
cable designation	LI9YH-Y 4x0.75			
wire length	2 m			
electrical data				
operating voltage / RMS value	300 V			
conductor cross section / of the power line	0.75 mm²			
mechanical data				
number of electrical cores	4			
type of electrical connection	M12-180			
outer diameter				
 of inner conductor 	1.1 mm			
 of the wire insulation 	1.7 mm			
of cable sheath	5.7 mm			
symmetrical tolerance of the outer diameter / of cable sheath	0.2 mm			
design of stranding element	Pairs			
conductor class	5			
material				
 of the conductor 	CU, blank			
 of the wire insulation 	PP			
of cable sheath	PVC			
product component / PE connection	No			
marking / of cores	Color			
color				
 of the power line insulation 	brown / white / blue / black			
of cable sheath	gray			
bending radius				
 with single bend / minimum permissible 	57 mm			
 with multiple bends / minimum permissible 	57 mm			
with continuous bending	57 mm			
number of bending cycles	100000			
tensile load / maximum	15 N			
weight per length	54 kg/km			
plug				
type of plug interlock	screwed			
design of plug-in connection	M12-90			

connector coding	M12	
connector coding / of the M12 circular connector	A coded	
ambient conditions		
ambient temperature		
 during operation 	-25 +80 °C	
 during storage 	-25 +80 °C	
 during transport 	-25 +80 °C	
during installation	80 °C	
ambient condition / for operation	With moving applications, the permissible operating temperature range is -5 to +80 degrees Celsius	
fire behavior	Flame-resistant acc. to UL 758 (CSA FT 1)	
chemical resistance		
to mineral oil	Conditional resistance	
• to grease	Conditional resistance	
radiological resistance / to UV radiation	not resistant	
protection class IP	IP65 / 67	
product features, product functions, product components	/ general	
product feature		
halogen-free	No	
• silicon-free	Yes	
standards, specifications, approvals		
certificate of suitability		
 EAC approval 	Yes	
 RoHS conformity 	Yes	
further information / internet-Links		
Internet-Link		
to web page: selection aid TIA Selection Tool	http://www.siemens.com/tia-selection-tool	
 to website: Industrial communication 	http://www.siemens.com/simatic-net	
to website: Industry Mall	https://mall.industry.siemens.com	
 to website: Information and Download Center 	http://www.siemens.com/industry/infocenter	
 to website: Selection guide for cables and connectors 	https://sie.ag/2QdlxcP	
 to website: Image database 	http://automation.siemens.com/bilddb	
to website: CAx-Download-Manager	http://www.siemens.com/cax	
 to website: Industry Online Support 	https://support.industry.siemens.com	

last modified: 7/7/2022 🖸