

443975-2 ✓ ACTIVE

AMPLIMITE

TE Internal #: 443975-2

Box Mount D-Sub Connectors, Receptacle, Round Termination

Post & Tail Diameter .76 mm [.03 in], Cable-to-Board, 15 Position, 2

Connector Shell Size

[View on TE.com >](#)



Connectors > D-Shaped Connectors > D-Sub Connectors > Box Mount D-Sub Connectors



Connector & Housing Type: **Receptacle**

Round Termination Post & Tail Diameter: **.76 mm [.03 in]**

Connector System: **Cable-to-Board**

Number of Positions: **15**

Power/Signal/Coax Combination: **No**

**Features**

**Product Type Features**

Connector & Housing Type	Receptacle
Connector System	Cable-to-Board
Connector Shell Size	2
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

**Configuration Features**

PCB Mount Orientation	Vertical
Number of Positions	15
Power/Signal/Coax Combination	No

**Body Features**

Rear Shell Material	Steel
Rear Shell Plating Material	Cadmium
Front Shell Plating Material	Cadmium
Front Shell Material	Steel
D-Sub Connector Insert Arrangement	MS18274-1

**Contact Features**

	10 µin
Contact Mating Area Plating Material	Gold



PCB Contact Termination Area Plating Material	Gold
Contact Base Material	Brass
Contact Type	Socket
Contact Size	Size 20
Contact Current Rating (Max)	5 A

### Termination Features

Termination Post & Tail Length	3.95 mm[.156 in]
Round Termination Post & Tail Diameter	.76 mm[.03 in]

### Mechanical Attachment

Mounting Hole Diameter	3.05 mm[.12 in]
Mating Alignment	Without

### Housing Features

Centerline (Pitch)	2.77 mm[.109 in]
--------------------	------------------

### Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

### Operation/Application

Circuit Application	Signal
---------------------	--------

### Packaging Features

Packaging Method	Package
------------------	---------

### Other

D-Shaped Connectors Comment	For solder dip product see part number 443975-7.
-----------------------------	--

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Cd (1.5%) Article Safe Usage Statements:



Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Customers Also Bought



TE Part #2102061-6  
Mezalok, Socket, 114 p, 10 mm, 30 Au, LF



TE Part #443975-4  
AMPLIMITE, RCPT ASY, POSTD, 109, 4



TE Part #1218124-4  
37 POS, ASSY, PLUG, LOW PROF, 109



TE Part #1218124-1  
9 POS, ASSY, PLUG, LOW PROF, 109



TE Part #1218124-3  
25 POS, ASSY, PLUG, LOW PROF, 109



TE Part #443975-1  
AMPLIMITE, RCPT ASY, POSTD, 109, 1




TE Part #YDIV44E15-05PNC009  
RECP ASSY



TE Part #YDIV44E17-26SNC009  
RECP ASSY



TE Part #ANT-916-SP  
Antenna SP PCB RPC 916MHz SMT



TE Part #175465-000  
TXR54AB90-1205AI

### Documents



### Product Drawings

[AMPLIMITE,RCPT ASY,POSTD,109,2](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_443975-2\\_F.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_443975-2\\_F.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_443975-2\\_F.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_443975-2\\_C.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_443975-2\\_C.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_443975-2\\_C.3d\\_stp.zip](#)

English

[3D PDF](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Agency Approvals

[UL Report](#)

English