



Energy & Power > Power Cable Accessories > Joints & Splices



Joints & Splice Product Availability: **AMERICAS**

Installation Instruction: **English**

Joints & Splice Technology: **Cold Applied, Cold Shrink**

Joints & Splice Voltage Class: **≤ 1 kV**

Joint & Splice Application Type: **Inline**

Features

Product Type Features

Component Design	PowerGel Sealing Gel
Adhesive Coating	Silicone Gel
Joints & Splice Technology	Cold Applied, Cold Shrink
Joints & Splice Product Type	Gel Tap Splice
Closing Method	Snap

Electrical Characteristics

Joints & Splice Voltage Class	≤ 1 kV
-------------------------------	-------------

Body Features

Color	Black
-------	-------

Mechanical Attachment

Mechanical Reinforcement	No
--------------------------	----

Dimensions

Conductor Size (All Outlets)	14 – 2 AWG
Height (Installed)	27 mm[1.06 in]
Width (Installed)	41 mm[1.63 in]
Length (Installed)	70 mm[2.75 in]
Cross-Section Range	2 – 35 mm ²
Cable Cross-Section (Max) (Main)	35 mm ²



Cable Cross-Section (Min) (Main)	2 mm ²
----------------------------------	-------------------

Usage Conditions

Environmental Resistance	Moisture, Weathering, Rain, Salt Water, Contaminated Water ...
--------------------------	--

Operating Temperature Range	-40 – 90 °C
-----------------------------	-------------

Chemical Resistance	Transformer Oil & Hydrocarbons (Both, Depending on Type, Conditions & Exposure Time)
---------------------	--

Operation/Application

Thermal Resistance	Applicable for Low Temperatures, Applicable for High Temperatures, Flame-Retardant
--------------------	--

Mechanical Resistance	Against Mechanical Impact
-----------------------	---------------------------

UV-Stabilized	Yes
---------------	-----

Joint & Splice Application Type	Inline
---------------------------------	--------

Free of Lead, Cadmium, Heavy Metals	Yes
-------------------------------------	-----

Industry Standards

CSA Certified	No
---------------	----

UL Rating	No
-----------	----

Product Availability

Joints & Splice Product Availability	AMERICAS
--------------------------------------	----------

Packaging Features

Packaging Quantity	18
--------------------	----

Packaging Method	Bag
------------------	-----

Other

Other Colors Available	No
------------------------	----

Product Use	PowerGel-filled box for LV underground & overhead tap splices.
-------------	--

Installation Instruction	English
--------------------------	---------

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 888615-000
GTAP-1(B72)



TE Part # 446451-000
GTAP-2(B18)



TE Part # 981609-000
GTAP-2(B72)

Also in the Series | RAYCHEM GTAP



Joints & Splices(3)

Customers Also Bought




TE Part #1-1609112-2
15CE1=F8272




TE Part #6648434-1
CONTACT,SKT,SIZE 1/4 (712-81-01107)



TE Part #901284-000
BCAC-5D/8-01(B12)



TE Part #120411-000
B-040-24-N



TE Part #1445692-4
ASY,PIN,QUADRAX



TE Part #650073-000
D-436-43

Documents

Datasheets & Catalog Pages

[GTAP-SPLICE-CABLE-ACCESSORIES](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English