


NBC-R4ACS/0,5-94C/OE - Patch cable



1113331

<https://www.phoenixcontact.com/us/products/1113331>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Patch cable, degree of protection: IP20, cable length: 0.5 m, number of positions: 8, 1 Gbps, CAT5, material: PP, connection method: Pierce connection, connection cross section: AWG 26-26, cable outlet: straight, Ethernet

Your advantages

- Perfect for industrial applications
- PUR cable for moving applications (bend)
- Worldwide approval with CE, UL, WEEE, and EAC
- Secure connection and disconnection with reliable locking clip protection
- Ideal EMC properties, thanks to 360° shielding
- Simultaneous power transmission with PoE++
- High-speed data transmission with up to 1 Gbps (CAT5)
- Resistant to shock and vibrations, thanks to robust molding

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1113331 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB11 |
| Product key | ABNABE |
| GTIN | 4063151036058 |
| Weight per piece (including packing) | 22.22 g |
| Weight per piece (excluding packing) | 41.148 g |
| Customs tariff number | 85444210 |
| Country of origin | PL |

1113331

<https://www.phoenixcontact.com/us/products/1113331>

Technical data

Product properties

| | |
|---------------------|-------------------------|
| Product type | Data cable preassembled |
| Sensor type | Ethernet |
| Number of positions | 8 |
| Shielded | yes |
| Cable outlet | straight |

Insulation characteristics

| | |
|----------------------|---|
| Overvoltage category | I |
| Degree of pollution | 2 |

Electrical properties

| | |
|-----------------------------------------|----------|
| Rated voltage (III/2) | 72 V |
| Rated current | 1.5 A |
| Insulation resistance | > 1 TΩ |
| Contact resistance | < 20 mΩ |
| Transmission characteristics (category) | CAT5 |
| Transmission speed | 100 Mbps |

Mechanical properties

Mechanical data

| | |
|-------------------------------------|---------|
| Insertion force per signal contact | 50.00 N |
| Extraction force per signal contact | 30 N |

Material specifications

| | |
|----------------------------------------|--------------|
| Flammability rating according to UL 94 | V2 |
| Contact material | CuSn6 |
| Contact surface material | Ni/Au |
| Contact carrier material | PC |
| Housing material | PP |
| Outer sheath, material | PUR |
| Conductor material | Copper, bare |

Dimensions

| | |
|--------|---------|
| Width | 13.8 mm |
| Height | 14.8 mm |
| Length | 44.2 mm |

Connection data

Connection technology

| | |
|-------------------|-------------------|
| Connection method | Pierce connection |
|-------------------|-------------------|

NBC-R4ACS/0,5-94C/OE - Patch cable



1113331

<https://www.phoenixcontact.com/us/products/1113331>

Conductor connection

| | |
|-------------------|-------------------|
| Connection method | Pierce connection |
|-------------------|-------------------|

Connector

Connection 1

| | |
|-----------------------------|--------------------|
| Type | Plug straight RJ45 |
| Shielded | yes |
| Handle color | black |
| Insertion/withdrawal cycles | ≥ 750 |
| Degree of protection | IP20 |
| Number of positions | 8 |
| Insertion/withdrawal cycles | 750 |


Connection 2

| | |
|---------------------|----------------|
| Type | free cable end |
| Number of positions | 8 |

Cable/line

| | |
|--------------|--------|
| Cable length | 0.50 m |
|--------------|--------|

Ethernet drag chain CAT5, 4-pair [94C]

| | |
|---------------------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Shielded | yes |
| UL AWM Style | 20963 (80°C/30 V) |
| Cable weight | 57 kg/km |
| Cable type | Ethernet drag chain CAT5, 4-pair |
| Short symbol | 9YC(ST)11Y |
| Cable type (abbreviation) | 94C |
| Signal type/category | Ethernet CAT5 (IEC 11801), 1 Gbps |
| Cable structure | 4x2xAWG26/19, S/UTP |
| External cable diameter | 6.9 mm +0.1 mm ... 0.2 mm |
| Outer sheath, material | PUR |
| External sheath, color | water blue RAL 5021 |
| Thickness, outer sheath | 0.85 mm |
| Conductor material | Bare Cu litz wires |
| Conductor structure signal line | 19x 0.10 mm |
| AWG signal line | 26 |

NBC-R4ACS/0,5-94C/OE - Patch cable



1113331

<https://www.phoenixcontact.com/us/products/1113331>

| | |
|------------------------------------------------------|----------------------------------------------------------------------------|
| Conductor cross section | 4x 2x 0.14 mm ² |
| Material wire insulation | PP |
| Wire diameter incl. insulation | 1 mm |
| Single wire, color | white/blue-blue, white/orange-orange, white/green-green, white/brown-brown |
| Twisted pairs | 2 cores to the pair |
| Overall twist | Four pairs and four fillers to the core |
| Shielding | Tinned copper braided shield |
| Optical shield covering | 90 % |
| Nominal voltage, cable | ≤ 100 V |
| Test voltage Core/Core | 700 V (50 Hz, 1 min.) |
| Test voltage Core/Shield | 700 V (50 Hz, 1 min.) |
| Cable insulation resistance | ≥ 500 MΩ*km |
| Coupling resistance | ≤ 100.00 mΩ/m (at 10 MHz) |
| Wave impedance | 100 Ω ±5 Ω (at 100 MHz) |
| Loop resistance | ≤ 290.00 Ω/km |
| Cable capacity | approx. 50 nF/km (at 1 kHz) |
| Signal runtime | 5.3 ns/m |
| Tensile strength | ≤ 100 N |
| Minimum bending radius, fixed installation | 4 x D |
| Minimum bending radius, flexible installation | 8 x D |
| Number of bending cycles | 5000000 |
| Minimum bending radius, drag chain applications | 7,5 x D |
| Traversing rate | 3 m/s |
| Acceleration | 5 m/s ² |
| Damping | 3.2 dB (with 1 MHz) |
| | 6 dB (at 4 MHz) |
| | 9.5 dB (at 10 MHz) |
| | 12.1 dB (at 16 MHz) |
| | 13.6 dB (at 20 MHz) |
| | 17.1 dB (at 31.25 MHz) |
| | 24.8 dB (at 62.5 MHz) |
| | 32 dB (at 100 MHz) |
| Near end crosstalk attenuation (NEXT) | 65.3 dB (with 1 MHz) |
| | 56.3 dB (at 4 MHz) |
| | 50.3 dB (at 10 MHz) |
| | 47.2 dB (at 16 MHz) |
| | 45.8 dB (at 20 MHz) |
| | 42.9 dB (at 31.25 MHz) |
| | 38.4 dB (at 62.5 MHz) |
| | 35.3 dB (at 100 MHz) |
| Power-summed near end crosstalk attenuation (PSNEXT) | 62.3 dB (with 1 MHz) |
| | 53.3 dB (at 4 MHz) |
| | 47.3 dB (at 10 MHz) |

NBC-R4ACS/0,5-94C/OE - Patch cable



1113331

<https://www.phoenixcontact.com/us/products/1113331>

| | |
|---------------------------------|-------------------------------------------------|
| | 44.2 dB (at 16 MHz) |
| | 42.8 dB (at 20 MHz) |
| | 39.9 dB (at 31.25 MHz) |
| | 35.4 dB (at 62.5 MHz) |
| | 32.3 dB (at 100 MHz) |
| Return loss (RL) | 23 dB (at 4 MHz) |
| | 24.1 dB (at 8 MHz) |
| | 25 dB (at 10 MHz) |
| | 25 dB (at 16 MHz) |
| | 25 dB (at 20 MHz) |
| | 23.6 dB (at 31.25 MHz) |
| | 21.5 dB (at 62.5 MHz) |
| | 20.1 dB (at 100 MHz) |
| Halogen-free | according to IEC 60754-1 |
| Resistance to oil | in accordance with EN 60811-2-1 |
| Flame resistance | according to IEC 60332-1-2 |
| Ambient temperature (operation) | -20 °C ... 80 °C (Cable, flexible installation) |
| | -40 °C ... 80 °C (cable, fixed installation) |

Environmental and real-life conditions

Ambient conditions

| | |
|-----------------------------------------|-----------------------------------|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -40 °C ... 85 °C (RJ45 connector) |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C (RJ45 connector) |

NBC-R4ACS/0,5-94C/OE - Patch cable



1113331

<https://www.phoenixcontact.com/us/products/1113331>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-11.0 | 27060308 |
| ECLASS-12.0 | 27060308 |
| ECLASS-13.0 | 27060308 |

ETIM

| | |
|----------|----------|
| ETIM 8.0 | EC002599 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

NBC-R4ACS/0,5-94C/OE - Patch cable



1113331

<https://www.phoenixcontact.com/us/products/1113331>

Environmental product compliance

| | |
|------------|-----------------------------------------------------------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e No hazardous substances above threshold values |
|------------|-----------------------------------------------------------------------------------------------------------|

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com