



SEC:A-A




SEC:B-B



Ordering Information & Specifications

Part No.	Wire Range	Insulation O.D.	Material	Finish	Q'ty/Reel
A2004-TPE-B	AWG#22-#28	1.50mm(max)	Phosphor Bronze	Tin-plated	10,000pcs
A2004-GPE-B	AWG#22-#28	1.50mm(max)	Phosphor Bronze	Gold-flash	10,000pcs

Note:E-Stamping before Tin-plated or Gold-plated

 燦達電子工業股份有限公司 JOINT TECH ELECTRONIC IND. CO., LTD.											
UNIT	SCALE	SHEET	TITLE:								
mm	1 : 1	1 of 1	2.00mm PITCH CRIMP TERMINAL								
DRAWN BY		APPROVED BY									
歐陽小強		謝瑞清									
2008.01.08		2008.01.08									
GENERAL TOLERANCE											
A4	EN1902180001	2019.02.18	周傑亮	<table border="1" style="width: 100%;"> <tr> <td colspan="2">DRAW NO. :</td> <td>REV.</td> </tr> <tr> <td colspan="2">A2004-XX-B</td> <td>A4</td> </tr> </table>		DRAW NO. :		REV.	A2004-XX-B		A4
DRAW NO. :		REV.									
A2004-XX-B		A4									
A3	EN1309120332	2013.09.05	郭本思								
A2	EN1108080346	2011.08.10	陳敏								
REV.	DESCRIPTION	DATE	NAME	<table border="1" style="width: 100%;"> <tr> <td>X. X±0.25</td> <td>ANGLE±</td> </tr> <tr> <td>X. XX±0.15</td> <td></td> </tr> <tr> <td>X. XXX±0.05</td> <td></td> </tr> </table>	X. X±0.25	ANGLE±	X. XX±0.15		X. XXX±0.05		
X. X±0.25	ANGLE±										
X. XX±0.15											
X. XXX±0.05											