## **SIEMENS**

Data sheet 6XV1850-2HH10


## product type designation

product description

## IE TP XP cord RJ45/RJ45, crossed

Crossover patch cable, preferred length, preassembled with two RJ45 connectors (10/100MB)

Industrial Ethernet TP XP Cord RJ45/RJ45, TP cord pre-assembled with 2 RJ45 plug, send and receive line crossed, length 1 m.



suitability for use	Easy connection of terminal devices to the IE FC cabling system	
cable designation	LI 02YSCY 2x2x0,15/0,98 PIMF ICCS GN	
wire length	1 m	
electrical data		
number of electrical connections	2	
attenuation factor per length		
<ul><li>at 10 MHz / maximum</li></ul>	0.09 dB/m	
<ul><li>at 100 MHz / maximum</li></ul>	0.285 dB/m	
<ul><li>at 300 MHz / maximum</li></ul>	0.495 dB/m	
• at 600 MHz / maximum	0.75 dB/m	
impedance		
at 1 MHz 100 MHz	100 Ω	
• at 10 MHz 600 MHz	100 Ω	
relative symmetrical tolerance		
<ul> <li>of the characteristic impedance at 1 MHz 100 MHz</li> </ul>	15 %	
<ul> <li>of the characteristic impedance at 10 MHz 600 MHz</li> </ul>	6 %	
transfer impedance per length / at 10 MHz	10 mΩ/m	
loop resistance per length / maximum	300 mΩ/m	
insulation resistance coefficient	150 GΩ·m	
operating voltage		
<ul> <li>RMS value</li> </ul>	80 V	
mechanical data		
number of electrical cores	4	
design of the shield	Overlapped aluminum-clad foil, sheathed in a braided screen of tin- plated copper wires	
core diameter		
of AWG26 insulated conductor	0.48 mm	
outer diameter		
<ul> <li>of inner conductor</li> </ul>	0.48 mm	
of the wire insulation	0.98 mm	
width / of cable sheath	5.8 mm	
symmetrical tolerance of width / of cable sheath	0.2 mm	
thickness / of cable sheath	3.7 mm	
symmetrical tolerance of thickness / of cable sheath	0.2 mm	
material		

	1 (1 1 (25)
of the wire insulation	polyethylene (PE)
of cable sheath	PVC
color	
of the insulation of data wires	white/blue, white/orange
of cable sheath	green
bending radius	
<ul><li>with single bend / minimum permissible</li></ul>	24 mm
with multiple bends / minimum permissible	42 mm
weight per length	32 kg/km
ambient conditions	
ambient temperature	
during operation	-40 +70 °C
during storage	-40 +70 °C
during transport	-40 +70 °C
during installation	-40 +70 °C
fire behavior	flame resistant according to IEC 60332-2-1
chemical resistance	
• to mineral oil	oil resistant according to IEC 60811-2-1 (4 h / 70°C)
• to grease	Conditional resistance
protection class IP	IP20
product features, product functions, product components	/ general
product feature	
• halogen-free	No
• silicon-free	Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	No
UL/ETL style / 600 V Rating	No
certificate of suitability	140
EAC approval	Yes
UL approval	Yes
standard for structured cabling	Cat5
Marine classification association	Caio
	No
<ul> <li>American Bureau of Shipping Europe Ltd. (ABS)</li> <li>French marine classification society (BV)</li> </ul>	No No
• • •	No No
Det Norske Veritas (DNV)	No No
Germanische Lloyd (GL)	No
Lloyds Register of Shipping (LRS)	No
Nippon Kaiji Kyokai (NK)      Nippon Kaiji Kyokai (NK)      Nippon Kaiji Kyokai (NK)	No 
Polski Rejestr Statkow (PRS)	No
reference code	
• according to IEC 81346-2	WG
• according to IEC 81346-2:2019	WGB
further information / internet-Links	
Internet-Link	
<ul> <li>to web page: selection aid TIA Selection Tool</li> </ul>	http://www.siemens.com/tia-selection-tool
<ul> <li>to website: Industrial communication</li> </ul>	http://www.siemens.com/simatic-net
• to website: Industry Mall	https://mall.industry.siemens.com
<ul> <li>to website: Information and Download Center</li> </ul>	http://www.siemens.com/industry/infocenter
<ul> <li>to website: Selection guide for cables and connectors</li> </ul>	https://sie.ag/2QdlxcP
<ul> <li>to website: Image database</li> </ul>	http://automation.siemens.com/bilddb
• to website: CAx-Download-Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

last modified:

7/7/2022