

## Product: <u>9423MN</u> I

# SpaceMaker™, 9 C #22 Str TC, PO Ins, PVC Jkt, AWM 2937



😭 Request Sample

### **Product Description**

SpaceMaker™, 9 Conductor 22AWG (19x34) Tinned Copper, PO Insulation, PVC Outer Jacket, AWM 2937

#### **Technical Specifications**

#### Construction Details

Conductor							
Element	Number of Elemen	nt Size	Stranding	Material			
Conductor(s)	9	22 AWG	19x34	TC - Tinned Copper			
nsulation							
Element	Material	Nom. Thi	ckness N	om. Insulation Diame	eter	Color Co	de
Conductor(s)	PP - Polypropylene	0.010 in (0	0.25 mm) 0.	050 in (1.3 mm)	Black, White, I	Red, Dark Green, Brown, I	Dark Blue, Orange, Yellow, Purp
Outer Shield							
Material							
No Shield							
Outer Jacket							
Mater	ial Nom. 1	hickness	Nom. Diam	eter			
PVC - Polyvin	yl Chloride 0.016 in	(0.41 mm)	0.213 in				
Overall Cable	Diameter (Nominal)	0.213 in.					
Electrical (	Characteristics						
		;					
Electricals		;					
Nom. Conduc	ctor DCR Nom. Ca	pacitance C	Cond-to-Cor			Max. Current	
	ctor DCR Nom. Ca			Nom. Characteris		Max. Current 1 Amps per Conductor at 2	25°C
Nom. Conduc	ctor DCR Nom. Ca	pacitance C					25°C
Nom. Conduc 18.1 Ohm/100	oft DCR Nom. Ca	pacitance C					25°C
Nom. Conduc 18.1 Ohm/100 /oltage	oft DCR Nom. Ca	pacitance C					25°C
Nom. Conduc 18.1 Ohm/100 /oltage UL Voltage R 300 V	oft DCR Nom. Ca	pacitance ( t (54.5 pF/m					25°C
Nom. Conduc 18.1 Ohm/100 /oltage UL Voltage R 300 V Mechanica	oft DCR Nom. Ca Oft 16.6 pF/f	pacitance ( t (54.5 pF/m					25°C
Nom. Conduct 18.1 Ohm/100 Voltage UL Voltage R 300 V Mechanica	oft DCR Nom. Ca Oft 16.6 pF/f ating	pacitance ( t (54.5 pF/m					25°C
Nom. Conduct 18.1 Ohm/100 Voltage UL Voltage R 300 V Mechanica Femperature UL Temperat	otor DCR Nom. Ca 10ft 16.6 pF/f ating I Characteristi	pacitance C t (54.5 pF/m CS					25°C
Nom. Conduct 18.1 Ohm/100 Voltage UL Voltage R 300 V Mechanica	oft DCR Nom. Ca Oft 16.6 pF/f ating	pacitance C t (54.5 pF/m CS					25°C
Nom. Conduct 18.1 Ohm/100 Voltage UL Voltage R 300 V Mechanica Femperature UL Temperatu 80°C Bend Radius	etor DCR Nom. Ca 10ft 16.6 pF/f ating I Characteristic ure Operating -20°C To +80°0	pacitance C t (54.5 pF/m CS	)				25°C
Nom. Conduct 18.1 Ohm/100 Voltage UL Voltage R 300 V Mechanica Femperature UL Temperature 80°C Bend Radius	tor DCR Nom. Ca 10ft 16.6 pF/f 16.6 pF/f 10ft	pacitance C t (54.5 pF/m CS	) xing Min.	51 Ohm			25°C
Nom. Conduct 18.1 Ohm/100 Voltage UL Voltage R 300 V Mechanica Femperature UL Temperature 80°C Stationary M 0.850 in (21.6	tor DCR Nom. Ca 16.6 pF/f 16.6 pF/f 10 Characteristic Nome Content of the second s	pacitance C t (54.5 pF/m CS 1in. Fle 2.130 i	) xing Min. n (54.10 mm	51 Ohm			25°C
Nom. Conduct 18.1 Ohm/100 Voltage UL Voltage R 300 V Mechanica Femperature UL Temperature 80°C Stationary M 0.850 in (21.6 Max. Pull Tem	etor DCR Nom. Ca 10ft 16.6 pF/f ating I Characteristic Ure Operating -20°C To +80°( 11. Installation for mm) 0.850 in sion:	pacitance C t (54.5 pF/m CS Nin. Fle 2.130 i 85.5 lbs (3	) xing Min. n (54.10 mm i8.8 kg)	51 Ohm			25°C
Nom. Conduct 18.1 Ohm/100 Voltage UL Voltage R 300 V Mechanica Femperature UL Temperature 80°C Stationary M 0.850 in (21.6	etor DCR Nom. Ca 10ft 16.6 pF/f ating I Characteristic Ure Operating -20°C To +80°( 11. Installation for mm) 0.850 in sion:	pacitance C t (54.5 pF/m CS 1in. Fle 2.130 i	) xing Min. n (54.10 mm i8.8 kg)	51 Ohm			25°C

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	FT2
AWM Compliance:	AWM 2937
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
Other Standard Compliance(s):	NFPA 79

#### **History**

Update and Revision:

Revision Number: 0.202 Revision Date: 05-05-2023

#### **Part Numbers**

Variants

ltem #	Color	Putup Type	Length	UPC
9423MN 006100	Blue, Light	Reel	100 ft	612825391913
9423MN 0061000	Blue, Light	Reel	1,000 ft	612825391920
9423MN 008100	Gray	Reel	100 ft	612825391937
9423MN 0081000	Gray	Reel	1,000 ft	612825391944
9423MN 004100	Yellow	Reel	100 ft	612825391890
9423MN 0041000	Yellow	Reel	1,000 ft	612825391906

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or guality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulators based on their individual usage of the product.