Ratings Voltage: 300 V Temperature: -80~200 °C Flammability: VW-1 Oil resistance: 60 °C

≥50% elongation and tensile strength after aging

## Conductor

Conductor count: 1 Gauge: 14 AWG 2.04 mm<sup>2</sup> Material: tinned copper strands Strand size: Ø 0.37mm x 19 Resistance at 20 °C: 8.96  $\Omega$  /km max

Material: Fluorinated ethylene propylene (FEP) Color: red


Diameter:  $\emptyset$  2.51  $\pm$  0.1 Nominal thickness: 0.33 mm Resistance at 20 °C: 2.5 M $\Omega$  /kft min

Wire marking: E339579 UL AWM STYLE 1332 14AWG 200°C 300V VW-1 - - - cUL AWM I A/B 200°C 300V FT1 TENSILITY

## **Mechanical Tests**

After aging at 232±1°C for 7 days
Minimum tensile strength 1.76 kgf/mm²
Minimum elongation 200% original





Revision:	Date:	Description:	Prepared:	Notes:				
A	05/25/2022	Initial release		RoHS compliant		$\vdash$ $I$	JSII	ITY
			Dimensions are in millimeters.	Function test: no open, no short circuit, no Intermittent	tel 1.541.323.3228 800 877.670.7118 fax 1.541.323.4202 web tensility.com			
				Description: Wire, hook-up, TS, 14 AWG, UL 1332, 300V, 200C,	Size: Part number: A 30-02521			
				2.51 mm, FEP, red		15:1		Sheet 1 of 1

3228 or a custom version of this cable assembly, call Tensility at 541-323-

email engineering@tensility.com