

ATGBICS MTP Female-Female 8 Fibres OM4 50/125 Multimode Trunk Cable, Type B, LSZH 2.0, 2m

Brand : ATGBICS

Product code: TCAB-8MTPFF-OM4-2M

Product name : ATGBICS MTP Female-Female 8 Fibres OM4 50/125 Multimode Trunk Cable, Type B, LSZH 2.0, 2m



ATGBICS MTP Female-Female 8 Fibres OM4 50/125 Multimode Trunk Cable, Type B, LSZH 3.0, 2m

ATGBICS MTP Female-Female 8 Fibres OM4 50/125 Multimode Trunk Cable, Type B, LSZH 2.0, 2m:

This product is high quality MTP Trunk Cable providing the backbone for Data Centre cabling. Due to its 3mm diameter they are space saving, ease cable management problems and optimise the Data Centre airflow. This is an OM4 8-fibre cable over multimode, used for 40G QSFP+ SR4/CSR4 or QSFP28 100G SR4 direct connection and high-density data centre applications. The MPO connection interface has been defined within the IEC-61754-7 international standards. Our products are rigorously tested and we proudly offer a compatibility guarantee and lifetime warranty.

Note: The US Conec MTP connectors are fully compliant with the MPO standards, achieving higher performance levels when compared to generic MPO connectors. MTP connector is a registered trademark of US Conec.



| Features | | Features | |
|-------------------------|---|-------------------------------|-------------------------------|
| Cable length * | 2 m | Insertion loss | 0.35 dB |
| Connector 1 * | MTP | Return loss | 50 dB |
| Connector 2 * | MTP | Jacket material * | Low smoke zero halogen (LSZH) |
| Connector 1 gender * | Female | Polarity | B |
| Connector 2 gender * | Female | Country of origin | China |
| Fibre optic type * | OM4 | Technical details | |
| Product colour * | Violet | Sustainability certificates | RoHS |
| Full duplex | ✗ | Doesn't contain | Halogen |
| Core diameter | 50 µm | Operational conditions | |
| Cladding diameter | 125 µm | Operating temperature (T-T) | -10 - 70 °C |
| Fiber mode structure | Multi-mode | Storage temperature (T-T) | -40 - 85 °C |
| Wavelengths supported | 850,1300 nm | Packaging data | |
| Ethernet interface type | 40 Gigabit Ethernet, 100 Gigabit Ethernet | Quantity per pack | 1 pc(s) |



5056468746092

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 21-SEP-2023. Prints or copies of Information are only valid on the printed Publication date