



**Product:** <u>1242A</u> ☑

Audio, Control & Instrument Cable, #22-4C, CM

# **Product Description**

Audio, Control & Instrument Cable, 4-22 AWG Solid Bare Copper Conductors, Polyolefin Insulated, PVC Jacket, CM Rated

# **Technical Specifications**

## **Product Overview**

Suitable Applications: low voltage analog signals (4-20ma, 0-10v, ...); low voltage control (24v, ...); line level audio; voice communications; panel wiring

## **Construction Details**

#### Conductor

Element	Number of Element	Size	Stranding	Material
Conductor(s)	4	22 AWG	Solid	BC - Bare Copper

#### Insulation

Element Material	Nom. Thickness	Nom. Insulation Diameter	Color Code	
Conductor(s)	PO - Polyolefin	0.009 in (0.23 mm)	0.0433 in mm	Green, Red, Yellow, Black

## Outer Shield

Material No Shield

## Outer Jacket

	Material	Nom. Imckiess	Noill. Diameter
	PVC - Polyvinyl Chloride	0.025 in (0.64 mm)	0.154 in (3.91 mm)
Ī	Overall Cable Diameter (I	Nominal): 0.154 in (	3.91 mm)

# **Electrical Characteristics**

## Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Velocity of Prop.	Max. Current
17.8 Ohm/1000ft	15 pF/ft (49 pF/m)	66%	2.2 Amps per Conductor at 25°C

## Voltage

UL Voltage Rating 300 V

## **Mechanical Characteristics**

#### Temperature

UL Temperature	Operating		
60°C	-20°C to +60°C		

# Bend Radius

Stationary Min.	Installation Min.
1.54 in (39.1 mm)	1.54 in (39.1 mm)

Max. Pull Tension: 32 lbs (15 kg)

#### **Standards and Compliance**

Environmental Suitability:	Indoor - Riser, Indoor	
Flammability / Reaction to Fire:	JL 1685 UL Loading, UL 1685 Vertical Tray, IEC 60332-1-2	
CPR Compliance:	CPR Euroclass: Eca	
NEC / UL Compliance:	Article 800, CM	
CEC / C(UL) Compliance:	CM	
Data Category:	Category 3	
UK Regulation Compliance:	UKCA Mark	

#### History

Update and Revision:	Revision Number: 0.400 Revision Date: 03-04-2023	

## **Part Numbers**

## Variants

Item #	Color	Putup Type	Length	UPC
1242A T35U1000	Beige, Pale Fawn	UnReel	1,000 ft	612825109686
1242A 008U1000	Gray	UnReel	1,000 ft	612825109693

#### © 2023 Belden, Inc

#### All Rights Reserved

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.