



**Product:** [8734](#)

Electronic, 3 C #22 Str TC, PVC Ins, 1C w/ TC Brd, PVC Jkt, CM

[Request Sample](#)

## Product Description

Electronic, 3 Conductor 22AWG (7x30) Tinned Copper, PVC Insulation, 1 Conductor w/ Tinned Copper Braid(80%) Shield, PVC Outer Jacket, CM

## Technical Specifications

### Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage control (24v, ...); line level audio; voice communications; panel wiring
------------------------	---

### Construction Details

#### Conductor

Element	Number of Element	Size	Stranding	Material
Conductor(s)	2	22	7x30	TC - Tinned Copper

#### Insulation

Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
PVC - Polyvinyl Chloride	0.015 in (0.38 mm)	0.60 in (15 mm)	Black, Red, White

#### Inner Shield

Shield Type	Material	Coverage
Braid	Tinned Copper (TC)	80%

#### Outer Shield

Shield Type	Material	Coverage
Braid	Tinned Copper (TC)	90%

#### Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.025 in (0.64 mm)	0.194 in

### Electrical Characteristics

#### Electricals

Nom. Conductor DCR	Max. Conductor DCR	Max. Current
10 Ohm/1000ft	15 Ohm/1000ft (49 Ohm/km)	2.9 Amps per Conductor at 25°C

#### Voltage

UL Voltage Rating
300 V

### Mechanical Characteristics

#### Temperature

UL Temperature	Operating
60°C	-20°C To +60°C

#### Bend Radius

Stationary Min.	Installation Min.
1.94 in (49.3 mm)	1.94 in

Max. Pull Tension:	18 lbs (8.2 kg)
Bulk Cable Weight:	22 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor, Outdoor
Flammability / Reaction to Fire:	UL1685 UL Loading, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CM
AWM Compliance:	AWM 2785
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## Product Notes

Notes:	Inner Shield over white conductor only.
--------	---

## History

Update and Revision:	Revision Number: 0.397 Revision Date: 05-05-2023
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC
8734 0601000	Chrome	Reel	1,000 ft	612825214779

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.