




Recommended P.C.B Layout(Top Side)  
(PCB BOARD TOLERANCE ± 0.05)



SPECIFICATIONS

Rated Current: 3.0AMP  
Contact Resistance: 20mΩ Max  
Withstand Voltage: 1000V AC/DC  
Insulation Resistance: 1000MΩ Min  
Operation Temperature: -40°C to +105°C

Contact Material: Brass  
Contact Plating: Au Or Tin Over Ni  
Insulator Material: Polyester(UL94V-0)  
Standard: PA6T  
Max. Processing Temp: 230°C for 30-60 seconds  
(260°C for 10 seconds)



Dimension antitheses list				
ITEM	PA	PB	PC	L
Standard	6.00	4.40	3.00	10.40
Alternate				

**Ordering Information**

XDZ 254 - \* - N - W - \* - \*\*

No. of Rows 1=Single Row 2=Dual Row	No. of Pins 02-40 Pin	Type Z=直针 W=弯针 S=插簧 WS=插簧	Length 毫米	Contact Plating G0:Gold Flash G1:1u" Gold G2:3u" Gold G3:5u" Gold G4:10u" Gold G5:15u" Gold G6:30u" Gold S0:Gold Flash/Tin S1:1in
---	--------------------------	---------------------------------------	--------------	--

			GENERAL TOLERANCE	制图 DRAWING	<b>深圳讯答科技有限公司</b> ShenzhenXundaTechnology Co.,Ltd			
			DIM TOL	审核 CHECK				
			X.X ± 0.30	批准 APPROVAL	产品名称 TITLE	2.54单排 正弯排针(塑高2.5)	版本 REV.	A
			X.XX ± 0.20	比例 SCALE	产品料号 PART NO.	XDZ254-1-N-W-2.5-XX	单位 UNITS	mm
			X.XXX ± 0.10	投影 Projection	材料 MATERIAL		页次 SHEET	1/1
1	初版发行	日期	Angle ± 3.0°					
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						