## **SIEMENS**

Data sheet 6XV1850-2HN10


## product type designation

product description

## IE TP XP cord RJ45/RJ45, crossed

Crossover patch cable, preferred length, preassembled with two RJ45 connectors (10/100MB)

Industrial Ethernet TP XP Cord RJ45/RJ45, TP cord pre-assembled with 2 RJ45 plug, send and receive line crossed, length 10 m.



suitability for use	Easy connection of terminal devices to the IE FC cabling system	
cable designation	LI 02YSCY 2x2x0,15/0,98 PIMF ICCS GN	
wire length	10 m	
electrical data		
number of electrical connections	2	
attenuation factor per length		
• at 10 MHz / maximum	0.09 dB/m	
<ul><li>at 100 MHz / maximum</li></ul>	0.285 dB/m	
• at 300 MHz / maximum	0.495 dB/m	
• at 600 MHz / maximum	0.75 dB/m	
impedance		
● at 1 MHz 100 MHz	100 Ω	
• at 10 MHz 600 MHz	100 Ω	
relative symmetrical tolerance		
• of the characteristic impedance at 1 MHz 100 MHz	15 %	
• of the characteristic impedance at 10 MHz 600 MHz	6 %	
transfer impedance per length / at 10 MHz	10 mΩ/m	
loop resistance per length / maximum	300 mΩ/m	
insulation resistance coefficient	150 GΩ·m	
operating voltage		
<ul> <li>RMS value</li> </ul>	80 V	
mechanical data		
number of electrical cores	4	
design of the shield	Overlapped aluminum-clad foil, sheathed in a braided screen of tin- plated copper wires	
core diameter		
<ul> <li>of AWG26 insulated conductor</li> </ul>	0.48 mm	
outer diameter		
<ul> <li>of inner conductor</li> </ul>	0.48 mm	
of the wire insulation	0.98 mm	
width / of cable sheath	5.8 mm	
symmetrical tolerance of width / of cable sheath	0.2 mm	
thickness / of cable sheath	3.7 mm	
symmetrical tolerance of thickness / of cable sheath	0.2 mm	
material		

of the wire insulation	polyethylene (PE)
of cable sheath	PVC
color	
of the insulation of data wires	white/blue, white/orange
of cable sheath	green
bending radius	
<ul><li>with single bend / minimum permissible</li></ul>	24 mm
with multiple bends / minimum permissible	42 mm
weight per length	32 kg/km
ambient conditions	
ambient temperature	
<ul> <li>during operation</li> </ul>	-40 +70 °C
during storage	-40 +70 °C
during transport	-40 +70 °C
during installation	-40 +70 °C
fire behavior	flame resistant according to IEC 60332-2-1
chemical resistance	0
• to mineral oil	oil resistant according to IEC 60811-2-1 (4 h / 70°C)
• to grease	Conditional resistance
protection class IP	IP20
product features, product functions, product components	
	<i>i</i> general
product feature	N.
• halogen-free	No
• silicon-free	Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	No
UL/ETL style / 600 V Rating	No
certificate of suitability	
<ul> <li>EAC approval</li> </ul>	Yes
UL approval	Yes
standard for structured cabling	Cat5
Marine classification association	
<ul> <li>American Bureau of Shipping Europe Ltd. (ABS)</li> </ul>	No
<ul> <li>French marine classification society (BV)</li> </ul>	No
<ul> <li>Det Norske Veritas (DNV)</li> </ul>	No
<ul> <li>Germanische Lloyd (GL)</li> </ul>	No
<ul> <li>Lloyds Register of Shipping (LRS)</li> </ul>	No
Nippon Kaiji Kyokai (NK)	No
Polski Rejestr Statkow (PRS)	No
reference code	
• according to IEC 81346-2	WG
• according to IEC 81346-2:2019	WGB
further information / internet-Links	
Internet-Link	
	http://www.siemens.com/tia-selection-tool
<ul> <li>to web page: selection aid TIA Selection Tool</li> <li>to website: Industrial communication</li> </ul>	http://www.siemens.com/simatic-net
to website: Industry Mall     to website: Information and Download Center	https://mall.industry.siemens.com
to website: Information and Download Center     to website: Selection guide for each and	http://www.siemens.com/industry/infocenter
<ul> <li>to website: Selection guide for cables and connectors</li> </ul>	https://sie.ag/2QdlxcP
to website: Image database	http://automation.siemens.com/bilddb
<ul><li>to website: CAx-Download-Manager</li></ul>	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

last modified:

7/7/2022