

## RG6/U Quad-Shield CMR-Rated Coaxial Cable, White, 1000 ft. (304.8 m)

MODEL NUMBER: A224-01K-WH



### Highlights

- Lower attenuation than RG59 cable for longer distances
- 18 AWG copper-clad steel center conductor
- Quad foil and braid shielding for error-free transmission
- Flame-retardant CMR-rated PVC jacket
- Meets UL1655, UL13, UL444 and RoHS standards

### Package Includes

- A224-01K-WH RG6/U Quad-Shield CMR-Rated Coaxial Cable, White, 1000-ft. (304.8 m)

Premium coaxial cabling designed for high-frequency indoor/outdoor applications, such as television antennas, digital cable and satellite transmissions, and video surveillance systems.

### Features

**Coaxial Cabling for High-Frequency Indoor/Outdoor Applications** Ideal for television antennas, digital cable and satellite transmissions, and video surveillance systems  
**White** 75-ohm cable tested to 3 GHz  
**Lower attenuation than RG59 cable for longer distances**  
**Premium Construction for Superior Performance** 18 AWG copper-clad steel center conductor Quad foil and braid shielding for error-free transmission  
**Flame-retardant CMR-rated PVC jacket** Meets UL1655, UL13, UL444 and RoHS standards

## Specifications

OVERVIEW	
UPC Code	037332196415
Technology	Coax; RG59/RG6
PHYSICAL	
Cable Jacket Color	White
Cable Jacket Material	PVC
Cable Jacket Rating	CMR
Cable Length (ft.)	1000
Cable Length (m)	304.88
Shipping Dimensions (hwd / in.)	9.45 x 20.87 x 20.87
Shipping Dimensions (hwd / cm)	24.00 x 53.01 x 53.01
Shipping Weight (lbs.)	35.00

Shipping Weight (kg)	15.88
<b>CONNECTIONS</b>	
Side A - Connector 1	BARE WIRE
Side B - Connector 1	BARE WIRE
Crossover Wiring	No
Connector Type	Bare Wire
Latching or Gripping Connector	No
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
IP68 Rated	No
Snagless Connector	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty