

USB-C to DVI Adapter Cable (USB-C to DVI-D Dual Link M/M), 1080p, 10 ft. (3.1 m)

MODEL NUMBER: U444-010-DE











USB-C to DVI converter connects a DVI display to your tablet, MacBook, Chromebook, Ultrabook or smartphone's USB-C or Thunderbolt 3 port.

Features

USB-C to DVI Adapter Connects to Your Laptop's USB-C or Thunderbolt 3 PortThis USB Type-C to DVI adapter connects a DVI monitor or projector to the USB-C or Thunderbolt 3 port on your computer, tablet, laptop, notebook, MacBook, Chromebook, Ultrabook or smartphone. It's an ideal connector for multitasking, presenting video at trade shows and conferences, editing documents, playing online games and watching movies on a larger screen. It saves you money by allowing you to use your existing DVI display instead of buying a new monitor.

Supports USB-C DisplayPort Alternate Mode for Transmitting Video SignalsBy connecting the USB-C cable to a source device that supports USB DisplayPort Alt Mode, you can output 1080p video to a compatible monitor or projector without installing special software drivers.

Transmits Crystal-Clear 1080p Video to a DVI DisplayConnect the dual-link DVI-D male connector to a compatible display to transmit high-definition video resolutions up to 1920 x 1200 (1080p) at 60 Hz. and 24-bit Deep Color (8 bits per channel).

Reversible USB-C Connector Attaches in Either DirectionUnlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for a fumble-free connection every time.

Ready to Use Right from the Package, So You Can Plug and Play Immediately The plug-and-play USB Type-C to DVI cable is specifically designed for use with the MacBook, Google Chromebook Pixel and other laptops, tablets and devices equipped with a USB-C or Thunderbolt 3 port. It requires no software, drivers or external power. The 10-ft. (3.05 m) (3-meter) length allows you great flexibility in placing the source and display devices where they're most convenient.

Highlights

- Transmits video signals from sources supporting USB DisplayPort Alt Mode
- Delivers HD picture quality at resolutions up to 1920 x 1200 (1080p) @ 60 Hz
- Plug-and-play operation with no software required for easy, immediate installation
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- 10-ft. (3.05 m) length allows great flexibility in placing source and display devices
- Note: This cable is unidirectional. Will only work from a USB-C port to DVI port

Applications

- Connect your laptop to a DVI monitor in a lecture hall or conference room for a video presentation
- Add a secondary monitor to the MacBook, Chromebook or laptop in your office or home workspace
- Stream online video or games from your computer on a larger DVI display

System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate
 Mode
- Display device with DVI input

Package Includes

 U444-010-DE USB-C to DVI Adapter Cable (M/M), White, 10ft. (3.05 m)

Specifications

OVERVIEW



UPC Code	037332238757	
Product Type	Passive Cable	
Technology	DVI	
Technology	DVI	
VIDEO		
Max Supported Video Resolution	1920 x 1200 (1080p)	
Max Supported Color Depth	24-bit True Color	
INPUT		
Bus Powered	Yes	
POWER		
USB Power Delivery (PD) Charging Support	No	
PHYSICAL		
Color	Black	
Material of Construction	PVC	
Cable Jacket Color	Black	
Cable Jacket Material	PVC	
Cable Jacket Rating	VW-1	
Cable Length (ft.)	10	
Cable Length (m)	3.05	
Cable Length (in.)	120	
Unit Dimensions (hwd / in.)	0.650 x 1.640 x 1.990	
Unit Packaging Type	Polybag	
ENVIRONMENTAL		
Operating Temperature Range	32 to 113 F (0 to 45 C)	
Storage Temperature Range	14 to 158 F (-10 to 70 C)	
Operating Humidity Range	10% to 85% RH	
Storage Humidity Range	5% to 90% RH	
CONNECTIONS		
Side A - Connector 1	DVI-D DUAL LINK (MALE)	
Side B - Connector 1	USB C (MALE)	
Connector Plating	Nickel	



FEATURES & SPECIFICATIONS		
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)	
IP68 Rated	No	
IP20 Rated	No	
UASP Support	No	
Auto MDIX Support	No	
Full Duplex Support	No	
Suspend Mode Support	No	
Remote Wakeup Support	No	
HDCP Specification	1.3	
Driver Required	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	1-year limited warranty	



© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.