

### Description

The CYMOC302X,CYMOC305X series of devices each consists of a GaAs infrared emitting diode optically coupled to a monolithic silicon photo Triac.

### Features

- Peak breakdown voltage,
  - 400V: CYMOC302X
    - 600V: CYMOC305X
- High isolation voltage between input and output (Viso=5000V rms )
- Compact dual-in-line package
- Pb free and RoHS compliant.

### Applications

- Isolated Line Receiver
- Solenoid/valve controls
- Light controls
- Static power switch
- AC motor drivers
- E.M. contactors
- Temperature controls
- AC Motor starters
- Solid state relays

### **Block Diagram and Package**



### Absolute Maximum Ratings (Ta=25°C)

	Parameter		Symbol	Rating	Unit	
Input	Forward Current		IF	60	mA	
	Reverse Voltage		VR	6	V	
	Power Dissipation		רות	100	mW	
	Derating Factor (above $Ta = 85^{\circ}C$ )		PD	3.8	mW/°C	
Output	Off-state Output	CYMOC302X	VDPM	400	V	
	Terminal Voltage	CYMOC305X		600		
	Peak Repetitive Sur (pw=100µs,120pps)	rge Current )	ITSM	1	А	
	On-State RMS Curr	rent	IT(RMS)	100	mA	
	Power Dissipation		РС	300	mW	
	Derating Factor (ab	ove $Ta = 85^{\circ}C$ )		7.4	mW/°C	
Total Power Dissipation			Ptot	330	mW	
Isolation Voltage *			Viso	5000	Vrms	
Operating Temperature			Topr	-55~+100	°C	
Storage Temperature			Tstg	-55~+125	°C	
Soldering Temperature (10s)			Tsol	260	°C	

\* AC for 1 minute, R.H.= 40 ~ 60% R.H. In this test, pins 1, 2 & 3 are shorted together, and pins 4, 5 & 6 are shorted together.



## Electrical Characteristics (Ta=25° C, unless specified otherwise)

Characteristics			Symbol	Condition	Min.	Тур.	Max.	Unit	
Input	Forward Voltage		VF	IF=20mA		1.18	1.5	V	
Input	Reverse Current		IR	VR=6V			10	μΑ	
	Peak Blocking Current		IDRM	VDRM=Rated VDRM, IF=0mA			100	nA	
	Peak On-state Voltage		VTM	ITM=100mA peak, IF=Rated IFT			2.5	V	
Output	Critical Rate of Rise off-state Voltage	CYMOC302X	dv/dt	VPEAK =Rated VDRM, IF=0	-	100	-	- V/μs	
		CYMOC305X	uvut	VPEAK =400V, IF=0	1000				
	Leakage in Inhibited State		IDRM2	IF= Rated IFT, VDRM=Rated, VDRM, off state			500	μΑ	
Transfer mA Characteristi cs	LED Trigger Current	CYMOC3021					15		
		CYMOC3051	IFT						
		CYMOC3022		Main terminal Voltage=3V				mA	
		CYMOC3052					10		
		CYMOC3023					5		
		CYMOC3053							
	Holding Current		IH			250		μΑ	









Fig.7 IDRM2, Leakage in Inhibit State VS Temperature

Fig.8 Inhibit Voltage vs. Temperature

**Test Circuits** 





The high voltage pulse is set to the required VPEAK value and applied to the D.U.T. output side through the RC circuit above. LED current is not applied. The waveform VT is monitored using an x100 scope probe. By varying RTEST, the dv/dt (slope) is increased, until the D.U.T. is observed to trigger (waveform collapses). The dv/dt is then decreased until the D.U.T. stops triggering. At this point,  $\tau RC$  is recorded and the dv/dt calculated.

$$dv/dt = \frac{0.632 \times V_{PEAK}}{\tau_{RC}}$$

For example, VPEAK = 400V for CYMOC302X series. The dv/dt value is calculated as follows:

$$dv/dt = \frac{0.632 \times 400}{\tau_{RC}} = \frac{252}{\tau_{RC}}$$

© CHEUK YUI INNOVATION CO., LIMITED Proprietary & Confidential



Unit: mm

#### **Solder Reflow Profile**



#### **Outline Dimensions**



#### 6-pin DIP



### 6-pin SMD

#### Attention:

•CHEUK YUI will continue to improve the quality, reliability, function or design and provide better products

,We reserve the right to modify this specification at any time without prior notice.

•Before placing an order, please confirm that the information on hand is the latest version, and the customer needs to confirm that the chip does meet their needs and can meet their requirements.

•Please comply with the product specifications for use, CHEUK YUI is not responsible for the quality problems caused by noncompliance with the product specifications during use.

•Products that require high reliability and are used for any of the above specific equipment or devices,

such as military, nuclear power control, medical, life support or life saving, may result in personal injury or death, For advice, please contact our sales representative

•Please take measures to prevent static damage when using this product.

• If you have any questions about the contents of this document, please feel free to contact us.