

USB 2.0 Panel Mount Cable, 5-Pin Motherboard IDC to USB-A (F/F), 3 ft. (0.91 m)

MODEL NUMBER: U024-003-5P-PM







Connects your computer's motherboard to a panel-mounted USB-A port that can be installed in a computer, booth, kiosk or podium.

Description

The U024-003-5P-PM USB 2.0 Hi-Speed Panel Mount Cable connects to a computer's motherboard to add a panel-mounted USB Type-A port. In addition to the front panel of a computer, the USB-A port can be installed in a trade show booth, retail kiosk or teacher's or lecturer's podium, allowing you to conveniently connect a thumb drive or other USB device. The PCB header terminates on almost any five-pin motherboard.

The 3-ft. (0.91 m) cable supports data transfer rates up to 480 Mbps and is backward compatible with previous USB generations. Gold-plated contacts resist corrosion and ensure optimal signal transfer. Premium double-shielded cables with aluminum braid and aluminum Mylar foil feature twisted 28 AWG data lines and 24 AWG power lines. PVC jacket with molded connectors and integral strain relief provides durability and long life. Mounting screws included.

Features

Adds a Panel-Mounted USB-A PortAllows convenient USB access from a trade show booth, retail kiosk or lecturer's podium5-pin PCB header terminates on computer's motherboardSupports data transfer speeds up to 480 MbpsBackward compatible with previous USB generations

Premium Construction for Premium PerformanceCorrosion-resistant gold-plated contacts for optimal signal transferFully molded construction with strain relief for durability and long lifeFlexible PVC jacket easy to install in tight spacesDouble shielding with aluminum braid, aluminum Mylar foil and twisted 28/24 AWG data/power linesMounting screws included

Specifications

| OVERVIEW | |
|------------|----------------------|
| UPC Code | 037332191113 |
| Technology | USB 2.0 (High Speed) |
| Cable Type | Passive |

Highlights

- Supports data transfer speeds up to 480 Mbps
- 5-pin PCB header connects to computer's motherboard
- USB-A port attaches with included screws
- Corrosion-resistant gold-plated contacts
- Backward compatible with previous USB generations

System Requirements

 Computer with 5-pin motherboard connector

Package Includes

- U024-003-5P-PM USB 2.0 Hi-Speed Panel Mount Cable, 3 ft.
- (2) Mounting screws



| PHYSICAL | |
|--|------------------------------|
| Cable Jacket Color | Black |
| Cable Length (ft.) | 3 |
| Cable Length (m) | 0.91 |
| Shipping Dimensions (hwd / in.) | 7.00 x 9.00 x 0.50 |
| Shipping Dimensions (hwd / cm) | 17.78 x 22.86 x 1.27 |
| Shipping Weight (lbs.) | 0.12 |
| Shipping Weight (kg) | 0.05 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 14° to 122°F (-10° to 50°C) |
| Storage Temperature Range | 5° to 140°F (-15° to 60°C) |
| Operating Humidity Range | 0% to 90% RH, Non-Condensing |
| Storage Humidity Range | 0% to 83% RH, Non-Condensing |
| CONNECTIONS | |
| Side A - Connector 1 | 5 PIN IDC (FEMALE) |
| Side B - Connector 1 | USB A (FEMALE) |
| Connector Style | Straight |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.