



Product: [DIW25](#)

Category 3 Backbone Cable, 25 Pair, U/UTP, CMR



Product Description

Category 3 Premise Backbone Cable (16MHz), DIW 25 Pair, 24 AWG Solid Bare Copper Conductors, U/UTP, Riser-CMR, PVC jacket

Technical Specifications

Product Overview

Suitable Applications:	Premise Backbone Cable, Ethernet 10BASE-T, Analog Phone, FAX
------------------------	--

Construction Details

Conductor

Size	Stranding	Material	Number of Pairs
24 AWG	Solid	BC - Bare Copper	25

Insulation

Material	Color Code
PVC - Polyvinyl Chloride	Western Electric

Outer Jacket

Material	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.380 in (9.65 mm)	Yes

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. Capacitance Unbalance
93.8 Ohm/km (28.6 Ohm/1000ft)	330 pF/100m

Delay

Frequency	Max. Delay	Max. Delay Skew	Nom. Velocity of Prop.
16 MHz	543 ns/100m	45 ns/100m	68%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. RL (Return Loss) [dB]	Max./Min. Fitted Impedance [Ohm]
0.772	2.2 dB/100m	47.0	43.0	50.1	46.1		
1	2.6 dB/100m	45.0	41.0	47.8	43.8	12.0	100 ± 15
4	5.6 dB/100m	36.0	32.0	36.0	32.0	12.0	100 ± 15
8	8.5 dB/100m	31.0	28.0	28.3	24.3	12.0	100 ± 15
10	9.7 dB/100m	30.0	26.0	26.2	22.3	12.0	100 ± 15
16	13.1 dB/100m	27.0	23.0	20.1	16.1	10.0	100 ± 15

Voltage

UL Voltage Rating
300 V (CMR)

Mechanical Characteristics

Temperature

UL Temperature	Operating	Installation	Storage
60°C	-30°C To +60°C	-30°C To +60°C	-30°C To +60°C

Bend Radius

Stationary Min.	Installation Min.
4.0 in (100 mm)	7.75 in (197 mm)

Max. Pull Tension:	150 lbs (68 kg)
Bulk Cable Weight:	100 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Riser, Indoor
Flammability / Reaction to Fire:	UL 1666 Riser, FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	CMR
CEC / C(UL) Compliance:	CMR
ICEA Compliance:	S-90-661
NEMA Compliance:	NEMA WC-63.1
Data Category:	Category 3
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 3
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	DPLN25

Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Print Includes Descending Footage/Meter Markings.
--------	--

History

Update and Revision:	Revision Number: 0.460 Revision Date: 01-20-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
DIW25 732CUT	Olive	Cut to Length		612825060611
DIW25 732CUT	Olive	Cut to Length	1 ft	612825060611
DIW25 732500	Olive	Reel	500 ft	612825060628
DIW25 732500	Olive	Reel	500 ft	612825060628
DIW25 7321000	Olive	Reel	1,000 ft	612825060635
DIW25 7321000	Olive	Reel	1,000 ft	612825060635
DIW25 732500B	Olive	Reel	1,500 ft	612825285533
DIW25 7325000	Olive	Reel	5,000 ft	612825060642
DIW25 7325000	Olive	Reel	5,000 ft	612825060642

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.