



FLEXO[®] STAINLESS STEEL XC
VIRTUALLY INDESTRUCTIBLE 304 STAINLESS STEEL
WILL NOT DISCOLOR OR RUST · TIGHT WEAVE FOR EXTRA COVERAGE

Our new X-tra Coverage product, Stainless Steel XC, provides fuller coverage with no transparent elements in the braided construction and results in a continuous stainless steel shine on any application. Nothing protects hoses from wear and blowout quite like real Stainless Steel braid. It looks great in any application and is as strong as, well, steel. But, custom hoses overbraided with stainless steel are expensive, selections are often limited and production and delivery times can be an issue. Now, you can take any stock or custom hose, slip a length of Flexo[®] Stainless over it, hide the cut ends under your clamps and have the same look and protection as custom overbraided hoses at a fraction of the cost. Flexo[®] Stainless XC is pre-rounded for easy, slip on installation and is available in diameters and expansion ranges to accommodate virtually any common hose or wire application.

SIZING CHART

Nominal Size	Part #	Wall Thickness	Wire Thickness	Min Expansion	Max Expansion	*Put-Ups		Available Colors	Lbs/100'
						M	L		
1/8"	SSL0.13SV	.013"	.005"	1/16"	11/32"	100'	250'	1	1.20
1/4"	SSL0.25SV	.013"	.005"	3/16"	13/32"	100'	250'	1	2.20
3/8"	SSL0.38SV	.013"	.005"	1/4"	5/8"	100'	250'	1	2.54
1/2"	SSL0.50SV	.013"	.005"	3/8"	3/4"	50'	100'	1	3.15
3/4"	SSL0.75SV	.013"	.005"	1/2"	1 1/4"	50'	100'	1	6.90
1"	SSL1.00SV	.025"	.010"	5/8"	1 5/16"	50'	100'	1	9.78
1 1/4"	SSL1.25SV	.025"	.010"	3/4"	1 3/4"	50'	100'	1	13.70
1 1/2"	SSL1.50SV	.025"	.010"	1"	2 1/8"	50'	100'	1	16.60

*Put-Ups: "M" = Shop Spool and "L" = Bulk Spool



FEATURES

Material	304 Stainless Steel
Grade	SSL
Wire Thickness	.005"-.010"
Drawing Number	TF001SSL-WD
Cutting	Shears

COLORS



Silver (SV)

CERTIFICATIONS





Nominal Size	Part #	AWG of Ends	Carriers	Wires/Carrier	Total Ends
1/8"	SSL0.13SV	36	24	5	120
1/4"	SSL0.25SV	36	24	13	312
3/8"	SSL0.38SV	36	48	7	336
1/2"	SSL0.50SV	36	48	11	528
3/4"	SSL0.75SV	36	48	15	720
1"	SSL1.00SV	30	48	7	336
1 1/4"	SSL1.25SV	30	48	10	480
1 1/2"	SSL1.50SV	30	48	12	576

PHYSICAL PROPERTIES

Wire Thickness (ASTM D-204)	.005"-.010"
Flammability Rating (SAEJ369)	Non Flammable
Recommended Cutting	Shears
Colors	1
Wall Thickness	.013"-.025"
Abrasion	Highs
Specific Gravity (ASTM D-792)	NA
Moisture Absorption % (ASTM D-570)	NA
Hard Vacuum Data (ASTM E-595 at 10-5 torr)	NA
TML	.00
CVCM	.00
WVR	.00
Smoke D-Max (ASTM E-662)	NA
Outgassing	Very Low
Oxygen Index (ASTM D-2863)	NA

FLAMMABILITY

Rating	Non Flammable
--------	---------------

OPERATING TEMPERATURES

Melt Point (ASTM D-2117)	2,650°F / 1,454°C
Maximum Continuous (Mil-I-23053)	°F / °C
Minimum Continuous (Mil-I-23053)	°F / °C

CHEMICAL RESISTANCE

1=No Effect 2=Little Effect 3=Affected 4=More Affected 5=Severely Affected

Aromatic Solvents	1
Aliphatic Solvents	1
Chlorinated Solvents	1
Weak Bases	1
Salts	2
Strong Bases	2
Salt Water (0-S-1926)	2
Hydraulic Fluid (MIL-H-5606)	1
Lube Oil (MIL-L-7808)	1
De-Icing Fluid (MIL-A-8243)	1
Strong Acids	2
Strong Oxidants	2
Esters/Ketones	1
UV Light	1
Petroleum	1
Fungus (ASTM G-21)	1
Halogen Free	Yes
RoHS	Yes
SVHC	NA

www.TECHFLEX.com

104 Demarest Road • Sparta, NJ 07871 • 1 (833) SLEEVING • (973) 300-9242 • fax: (973) 300-9409

© 2023 Techflex® - Any unauthorized reproduction, in whole or part, in any medium whatsoever, without the express written permission of Techflex® is strictly forbidden. Techflex® product names and logos are registered trademarks of Techflex®, unless otherwise attributed. The contents and illustrations contained herein are believed to be reliable. Techflex® makes no warranties as to their accuracy or completeness and disclaims any liability in connection with their use. Techflex's® only obligations are those in standard terms of sale for these products and Techflex® will not be liable for any consequential or other damages arising due to misuse of these products or typographical errors or omissions. Users should make their own evaluation to determine the suitability of these products for their unique and specific applications.

01-01-23