

Specification Sheet

Part Number: 156-00068



Friction tab inside the fir tree allows the tie to sit in mount without falling out prior to installation.

Fir tree provides low insertion effort yet demonstrates high extraction resistance.

Disc feature prevents rattling in high-vibration applications and protects against debris ingress.

Heavy Duty Cable Tie/Fir Tree Mount, 8.75 - 9.25 mm Hole Dia, 0.04 - 0.26" Panel Thickness, PA66HIRHSUV, Black,100/pkg

Article Number 156-00068

Type WSSFT9A

Color Black (BK)

Quantity Per bag

Product Description HellermannTyton's fir tree mounts provide a secure grip in a mounting hole. The mount can slide along the cable tie to adjust orientation as needed. Fir tree mounts are designed to provide a low insertion force and high extraction force. This mount is sold as an assembly with the cable tie.

Short Description Heavy Duty Cable Tie/Fir Tree Mount, 8.75 - 9.25 mm Hole Dia, 0.04 - 0.26" Panel Thickness, PA66HIRHSUV, Black,100/pkg

Global Part Name WSSFT9A-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial) 120.0

Minimum Tensile Strength (Metric) 535

Length L (Imperial) 9.0

Length L (Metric) 228.0

Fixation Method Fir Tree

Identification Plate Position none

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.5

Width W (Metric) 12.7

Bundle Diameter Max (Imperial) 2.3

Bundle Diameter Max (Metric) 57.0

Height H (Imperial) .75

Height H (Metric) 19.10

Panel Thickness Min (Imperial) 0.039

Panel Thickness Max (Imperial)	0.256
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	6.5
Mounting Hole Diameter D (Imperial)	0.34 - 0.36
Mounting Hole Diameter D (Metric)	8.7 - 9.2 mm
Mounting Hole Diameter D Min (Imperial)	0.34
Mounting Hole Diameter D Max (Imperial)	0.36
Mounting Hole Diameter D Max (Metric)	9.25
Disc Diameter (Metric)	21.6
Disc Diameter (Imperial)	0.9
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Material Cable Tie	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes

Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)