SIEMENS

Data sheet 6XV1870-3QN45

product type designation

product description



IE TP Cord RJ45/RJ45, 4x2

Patch cable, preferred length, preassembled with two RJ45 connectors (10/100/1000/10000MB)

Industrial Ethernet TP Cord RJ45/RJ45, CAT 6A, TP cable 4x2, preassembled with 2 RJ45 connectors, length 45 m.

suitability for use	Easy connection of terminal devices to the IE FC cabling system
cable designation	LI 02YSCH 4x2x0,15 PIMF GN FRNC
wire length	45 m
electrical data	
number of electrical connections	2
attenuation factor per length	
at 10 MHz / maximum	0.086 dB/m
at 100 MHz / maximum	0.28 dB/m
at 300 MHz / maximum	0.501 dB/m
at 600 MHz / maximum	0.735 dB/m
impedance	
at 1 MHz 100 MHz	100 Ω
● at 10 MHz 600 MHz	100 Ω
relative symmetrical tolerance	
 of the characteristic impedance at 1 MHz 100 MHz 	15 %
 of the characteristic impedance at 10 MHz 600 MHz 	10 %
transfer impedance per length / at 10 MHz	10 mΩ/m
loop resistance per length / maximum	290 mΩ/m
operating voltage	
RMS value	80 V
NVP value in percent	80 %
mechanical data	
number of electrical cores	8
design of the shield	Overlapped aluminum-clad foil, sheathed in a braided screen of tin- plated copper wires
core diameter	
of AWG26 insulated conductor	0.5 mm
outer diameter	
 of inner conductor 	0.5 mm
 of the wire insulation 	1 mm
of cable sheath	6.2 mm
symmetrical tolerance of the outer diameter / of cable sheath	0.3 mm
material	
of the wire insulation	polyethylene (PE)

of cable sheath	FRNC
color	
of the insulation of data wires	white/blue, white/orange, white/green, white/brown
of cable sheath	green
bending radius	
with single bend / minimum permissible	31 mm
with multiple bends / minimum permissible	43.5 mm
weight per length	50 kg/km
ambient conditions	
ambient temperature	
during operation	-25 +80 °C
during storage	-25 +80 °C
during transport	-25 +80 °C
during installation	-25 +80 °C
• note	In fixed installation -40 °C to 80 °C
fire behavior	flame resistant according to IEC 60332-1-2, smoke density according to IEC 61034
class of burning behaviour / according to EN 13501-6	Eca
chemical resistance	
• to mineral oil	oil resistant according to IEC 60811-2-1 (4 h / 70°C)
• to grease	Conditional resistance
radiological resistance / to UV radiation	not resistant
protection class IP	IP20
product features, product functions, product components	/ general
product feature	7 goriotal
halogen-free	Yes
• silicon-free	Yes
standards, specifications, approvals	1.00
	No
UL/ETL style / 600 V Rating	Yes; E130266 AWM STYLE 21279
UL/ETL style / 600 V Rating certificate of suitability	165, E130200 AVVIVI 311LE 21219
EAC approval	Yes
UL approval	Yes
RoHS conformity	Yes
standard for structured cabling	Cat6A
Marine classification association	OdioA
American Bureau of Shipping Europe Ltd. (ABS)	No
French marine classification society (BV)	No
Det Norske Veritas (DNV)	No
Germanische Lloyd (GL)	No
Lloyds Register of Shipping (LRS)	No
Nippon Kaiji Kyokai (NK)	No
Polski Rejestr Statkow (PRS)	No
reference code	
according to IEC 81346-2	WG
• according to IEC 81346-2:2019	WGB
further information / internet-Links	
Internet-Link	
to web page: selection aid TIA Selection Tool	http://www.siemens.com/tia-selection-tool
to web page. selection and TIA Selection Tool to website: Industrial communication	http://www.siemens.com/simatic-net
to website: Industrial communication to website: Industry Mall	https://mall.industry.siemens.com
to website: Industry Mail to website: Information and Download Center	http://www.siemens.com/industry/infocenter
to website: Selection guide for cables and connectors	https://sie.ag/2QdlxcP
to website: Image database	http://automation.siemens.com/bilddb
to website: Mage database to website: CAx-Download-Manager	http://www.siemens.com/cax
to website: CAX-Download-Manager to website: Industry Online Support	https://support.industry.siemens.com
To Website. Industry Offinite Support	mpostoupportainadotty.oiomono.com
last modified:	6/25/2022 🖸