



Product: [5300UH](#)

Security & Sound, 2 Conductor 18 AWG, TC, Riser

Product Description

Security & Commercial Audio Cable, 2 Conductor 18 AWG stranded (7x26) tinned copper conductors with polyolefin insulation, Riser, PVC jacket with ripcord.

Technical Specifications

Product Overview

Suitable Applications:	Monitor/Detection, Control Circuits, Initiating Circuits, Notification Circuits
------------------------	---

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
18	7x26	TC - Tinned Copper	2

Conductor Count:	2
------------------	---

Insulation

Material	Nominal Wall Thickness
PP - Polypropylene	0.008 in

Color Chart

Number	Color
1	Black
2	Red

Outer Shield

Material
No Shield

Outer Jacket

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.017 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
6.5 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor
21.5 pF/ft

Inductance

Nominal Inductance
0.145 μ H/ft

Current

Max. Recommended Current [A]

5 Amps per Conductor at 25°C

Voltage**UL Voltage Rating**

300 V RMS

Temperature Range

UL Temp Rating:	75°C
Operating Temperature Range:	-20°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	15 lbs/1000ft
Max. Pull Tension:	45 lbs
Min. Bend Radius/Minor Axis:	1.75 in

Standards

NEC Articles:	Article 800
NEC/(UL) Compliance:	CMR
CEC/C(UL) Compliance:	CMG

Applicable Environmental and Other Programs

Environmental Space:	Indoor - Riser
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1666 Vertical Shaft
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	N
Plenum Number:	6300UH

Related Part Numbers**Variants**

Item #	Color	Put-Up Type	Length	UPC
5300UH 0101000	Black	Reel	1,000 ft	612825159278
5300UH 010U1000	Black	UnReel	1,000 ft	612825421559
5300UH 010Z1000	Black	Reel/Tuff Box	1,000 ft	612825159360
5300UH 0081000	Gray	Reel	1,000 ft	612825159247
5300UH 008U1000	Gray	UnReel	1,000 ft	612825159261
5300UH 009U1000	White	UnReel	1,000 ft	612825159285

History

Update and Revision:	Revision Number: 0.237 Revision Date: 11-09-2022
----------------------	--

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

