

Product: 8465MN ☑



SpaceMaker™, 5 C #18 Str TC, PO Ins, PVC Jkt, AWM 2937

Request Sample

Product Description

SpaceMaker™, 5 Conductor 18AWG (41x34) Tinned Copper, PO Insulation, PVC Outer Jacket, AWM 2937

Technical Specifications

Construction Details

Element	Number of Element	Size	Stranding	Material
Conductor(s)	5	18 AWG	41x34	TC - Tinned Copper

Insulation

Conductor

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PP - Polypropylene	0.010 in (0.25 mm)	0.067 in (1.7 mm)	Black, White, Red, Green, Brown

Outer Shield

Material No Shield

Outer Jacket

	Material	Nom. Thickness	Nom. Diameter
	PVC - Polyvinyl Chloride	0.016 in (0.41 mm)	0.213 in
Ī	Overall Cable Diameter (I	Nominal): 0.213 in	

Electrical Characteristics

Electricals

Nom. Conductor DCR Nom. Capacitance Cond-to-Con		Nom. Characteristic Impedence	Max. Current
7.06 Ohm/1000ft	14.8 pF/ft (48.6 pF/m)	39 Ohm	4 Amps per Conductor at 25°C

Voltage

UL Voltage Rating

Mechanical Characteristics

Temperature

UL Temperature	Operating		
80°C	-20°C To +80°C		

Bend Radius

Stationary Min.	Installation Min
2.130 in (54.10 mm)	2.130 in
` `	
Max. Pull Tension:	10
Bulk Cable Weight:	36

Standards and Compliance

Environmental Suitability:	Indoor
AWM Compliance:	AWM 2937
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)

History

Update and Revision:	Revision Number: 0.142 Revision Date: 05-05-2023
opadio dila ricvisioni.	Trevision Trainiber. 6.142 Trevision Bate. 66 66 2020

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
8465MN 006100	Blue, Light	Reel	100 ft	612825387046
8465MN 0061000	Blue, Light	Reel	1,000 ft	612825387053
8465MN 008100	Gray	Reel	100 ft	612825387060
8465MN 0081000	Gray	Reel	1,000 ft	612825387077
8465MN 004100	Yellow	Reel	100 ft	612825387022
8465MN 0041000	Yellow	Reel	1,000 ft	612825387039

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.