Flexible Test Cable

FLC SMSM+ Series

50 Ω DC to 26 GHz

The Big Deal

- Ultra-wideband, DC to 26 GHz
- Minimal performance change versus flexure
- Low loss



CASE STYLE: MU1838

Product Overview

Mini-Circuits FLC-SMSM+ series flexible test cables provide ultra-wideband performance from DC to 26 GHz with low insertion loss and excellent VSWR. Specially designed for outstanding stability of phase and insertion loss versus flexure, these cables are ideal for demanding lab environments where crowded layouts and frequent bending are common. They feature SMA-M to SMA-M stainless steel connectors and rugged cable construction with protective shield and strain relief for excellent durability. Available from stock in a variety of lengths to support a range of requirements.

Key Features

Feature	Advantages
Ultra-wideband, DC to 26 GHz	Supports a wide range of test applications including R&D, military and defense, production test and more.
Excellent stability of phase and insertion loss versus flexure	FLC-series test cables have been tested in bend radii as tight as 2.4 inches to qualify minimal change in insertion loss, insertion phase, and VSWR, providing reliable performance in a wide range of configurations.
Low insertion loss	Allows accurate measurement with minimal compensation for the effects of the cable connection.
Performance qualified to 20,000 flexures	Like all Mini-Circuits test cables, FLC-series models have been performance qualified up to 20,000 bend cycles, ensuring outstanding durability and extra long life.

Flexible Test Cable

FLC-4FT-SMSM+

50Ω 4FT DC to 26 GHz

Maximum Ratings

Operating Temperature	-55°C to +85°C
Storage Temperature	-55°C to +85°C
Power Handling at 25°C	315W at 2 GHz
Sea Level	94W at 18 GHz
	56W at 26 GHz

Permanent damage may occur if any of these limits are exceeded.

Features

- · Low insertion loss, 3.3 dB at 26 GHz
- Rugged construction includes protective shield and strain relief for longer life
- · Stainless steel connectors for long mating-cycle life
- Extra flexible

Applications

- Military and defense applications
- · Research & development labs

Processor 155172


CASE STYLE: MU1838-4

Connectors Model
SMA Male FLC-4FT-SMSM+

+RoHS Compliant


The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Outline Drawing



OVERALL CONNECTOR DIMENSION

Outline Dimensions (inch)




Electrical Specifications at 25°C

Parameter	Condition (GHz)	Min.	Тур.	Max.	Units
Frequency Range		DC		26	GHz
Length ¹			4		ft
	DC - 6	_	1.40	3.9	
Insertion Loss	6 - 18	_	2.85	3.9	dB
	18 - 26	_	3.55	3.9	
	DC - 6	_	1.08	1.35	
VSWR	6 - 18	_	1.25	1.35	:1
	18 - 26	_	1.33	1.38	

Custom sizes available, consult factory.

Cable Construction





Product Guarantee

Mini-Circuits® will repair or replace your test cable at its option if the connector attachment fails within <u>six</u> months of shipment. This guarantee excludes cable or connector interface damage from misuse or abuse.


Performance Change vs. Flexure (Typical)²


Parameter	Condition (GHz)	Bend Radius (inches)			Units
raianietei		2.40			
	DC - 6	0.00	0.01	0.01	
Insertion Loss ³	6 - 18	0.01	0.02	0.03	dB
	18 - 26	0.01	0.04	0.05	
	DC - 6	0.03	0.09	0.49	
Insertion Phase ³	6 - 18	0.03	0.31	1.7	Deg
	18 - 26	0.07	1.6	2.9	
	DC - 6	0.00	0.01	0.01	
VSWR ³	6 - 18	0.01	0.02	0.02	:1
	18 - 26	0.01	0.08	0.11	

- 2. Performance change versus flexure with a 3 ft cable 360° around a 4" diameter mandrel.
- 3. Absolute values normalized to the reference position 0. See AN-46-003 under Associated Application Notes

Typical Performance Data

Frequency (GHz)	Insertion Loss (dB)	VSWR (:1)	
		SMA MALE 1	SMA MALE 2
0.1	0.20	1.01	1.02
1.0	0.54	1.05	1.06
2.0	0.77	1.07	1.08
4.0	1.11	1.04	1.04
6.0	1.36	1.06	1.06
8.0	1.63	1.12	1.11
10.0	1.74	1.14	1.12
12.0	1.94	1.10	1.10
14.0	2.17	1.10	1.09
16.0	2.47	1.14	1.13
18.0	2.80	1.27	1.21
20.0	2.96	1.26	1.20
22.0	2.94	1.19	1.15
24.0	3.22	1.15	1.11
26.0	3.33	1.16	1.20





Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

