


CATALOG NUMBER	MATERIAL NUMBER	CABLE RANGE	NOMINAL ROD DIAMETER	LENGTH "M"	LENGTH "B"	BREAK STRENGTH* (LBS/N)	UL LISTED	CSA APPROVED	PRODUCT SELECTION NUMBER
35901	1300950146	.50-.61 / 12.7-15.5	.56 / 14.2	11.0±1.50 / 279±38	5.0±0.50 / 127±13	3400 / 15124	NO	YES	PL050-1
35902	1300950147	.62-.74 / 15.7-18.8	.68 / 17.3	11.0±1.50 / 279±38	6.0±0.50 / 152±13	4100 / 18238			PL062-1
35903	1300950148	.75-.99 / 19.1-25.1	.87 / 22.1	13.0±1.50 / 330±38	6.0±0.50 / 152±13	4100 / 18238			PL075-1
35904	1300950149	1.00-1.24 / 25.4-31.5	1.12 / 28.4	14.0±1.50 / 356±38	7.0±1.00 / 178±25	5800 / 25800			PL100-1
35905	1300950150	1.25-1.49 / 31.8-37.8	1.37 / 34.8	15.0±2.00 / 381±51	7.0±1.00 / 178±25	5800 / 25800			PL125-1
35906	1300950151	1.50-1.74 / 1.50-44.2	1.62 / 41.1	16.0±2.00 / 406±51	7.0±1.00 / 178±25	7500 / 33362			PL150-1
35907	1300950152	1.75-1.99 / 44.5-50.5	1.87 / 47.5	18.0±2.00 / 457±51	8.0±1.00 / 203±25	10000 / 44482			PL175-1
35908	1300950153	2.00-2.49 / 50.8-63.2	2.25 / 57.2	19.0±2.00 / 483±51	9.0±1.00 / 229±25	10000 / 44482			PL200-1
35909	1300950154	2.50-2.99 / 63.5-75.9	2.75 / 69.9	19.0±2.00 / 483±51	10.0±1.00 / 254±25	13000 / 57827			PL250-1

*TO DETERMINE RECOMMENDED WORKING LOAD, DIVIDE BREAK STRENGTH BY 5.



ITEM	DESCRIPTION	MATERIAL	RELEASE SALES DRAWING EC NO: IPC2014-1487 DRWN: HRUIZ01 2014/05/13 CHKD: HKNEELAN 2014/05/13 APPR: JFMURPHY 2014/10/14 REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE INCH/MM		SCALE NTS	DESIGN UNITS INCH	THIRD ANGLE PROJECTION																											
				$\nabla=0$ $\sphericalangle=0$	<table border="1"> <tr> <td></td> <td>mm</td> <td>INCH</td> </tr> <tr> <td>4 PLACES</td> <td>±---</td> <td>±---</td> </tr> <tr> <td>3 PLACES</td> <td>±---</td> <td>±.005</td> </tr> <tr> <td>2 PLACES</td> <td>±.13</td> <td>±.010</td> </tr> <tr> <td>1 PLACE</td> <td>±.25</td> <td>±.020</td> </tr> </table>		mm	INCH	4 PLACES	±---	±---	3 PLACES	±---	±.005	2 PLACES	±.13	±.010	1 PLACE	±.25	±.020	<table border="1"> <tr> <td>DRAWN BY</td> <td>DATE</td> </tr> <tr> <td>HRUIZ01</td> <td>2014/05/13</td> </tr> <tr> <td>CHECKED BY</td> <td>DATE</td> </tr> <tr> <td>HKNEELAN</td> <td>2014/05/13</td> </tr> <tr> <td>APPROVED BY</td> <td>DATE</td> </tr> <tr> <td>JFMURPHY</td> <td>2014/10/14</td> </tr> </table>	DRAWN BY	DATE	HRUIZ01	2014/05/13	CHECKED BY	DATE	HKNEELAN	2014/05/13	APPROVED BY	DATE	JFMURPHY	2014/10/14	TITLE		PULLING GRIPS LIGHT DUTY FLEXIBLE EYE		
	mm	INCH																																				
4 PLACES	±---	±---																																				
3 PLACES	±---	±.005																																				
2 PLACES	±.13	±.010																																				
1 PLACE	±.25	±.020																																				
DRAWN BY	DATE																																					
HRUIZ01	2014/05/13																																					
CHECKED BY	DATE																																					
HKNEELAN	2014/05/13																																					
APPROVED BY	DATE																																					
JFMURPHY	2014/10/14																																					
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		MOLEX INCORPORATED DOCUMENT NO. SD-130095-101		SHEET NO. 1 OF 1																													
			SIZE A		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																	
1	WIRE MESH	GALVANIZED STEEL	A																																			
2	SHOULDER PROTECTOR	ALUMINUM																																				
3	FERRULE	ALUMINUM																																				
4	BALE WIRE	GALVANIZED STEEL																																				
5	LABEL	MYLAR																																				