



FullAXS Mini

TE Internal #: 2-2061980-0

Rugged Fiber Cable Assemblies, Fiber Optic Cable (FOCAB), .189 in [4.8 mm] Diameter, 2 Fibers, Blue, Blue, Black Cable, FullAXS Mini

[View on TE.com >](#)

Fiber Optics > Fiber Optic Cable Assemblies > Rugged Fiber Cable Assemblies



Fiber Optic Cable Type: **Fiber Optic Cable (FOCAB)**

Cable Assembly Fiber Diameter: **9/125 μm**

Outside Cable Diameter: **4.8 mm [.189 in]**

Number of Fibers: **2**

Connector Color (End A): **Blue**

Features

Product Type Features

Rugged Fiber Cable Assembly System	FullAXS Mini
Fiber Optic Cable Type	Fiber Optic Cable (FOCAB)
Fiber Optic Mode	Singlemode
Connector Type (End A)	FULLAXS MINI LC Duplex Plug
Connector Type (End B)	LC Duplex Plug
Cable Assembly Type	FULLAXS MINI LC Duplex to LC Duplex
Fiber Type	SM

Configuration Features

Number of Fibers	2
Cable Buffering	Semi-Tight Buffer

Body Features

Connector Color (End A)	Blue
Connector Color (End B)	Blue
Cable Color	Black
Boot Type (Right)	Bend Limiting
Boot Color (Left)	Blue
Boot Color (Right)	Blue

Dimensions

Cable Assembly Fiber Diameter	9/125 μ m
Outside Cable Diameter	4.8 mm[.189 in]

Other

Cable Assembly Length	20 m
-----------------------	------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | FullAXS Mini



Rugged Fiber Cable Assemblies(20)

Customers Also Bought




TE Part #1-2061980-0
FOSM GLARO LEAD 4.8 MM FXS
MINI 10M




TE Part #6-2213767-1
AV19 DPL 5A MOVE RING LED WHITE
12V



TE Part #2061933-1
FULLPOWER MINI FIELD INSTALL
ASSEMBLY



TE Part #3-582151-5
41 AMP BLADE RCPT HSG




TE Part #66010-3
AMP BLADE RECP LP MIL




TE Part #1-2176248-4
TJT 250W 150R 5%



TE Part #2061980-3
FOSM GLARO LEAD 4.8 MM FXS
MINI 3 M



TE Part #1-2176084-2
EP 7W (S) 680R 5%



TE Part #CB2009-000
GELWRAP-18/4-150UL(B6)



TE Part #2213414-1
NECTOR M 3P FH PIN HOUSING,
CODE A

Documents

Product Drawings

FOSM GLARO LEAD 4.8 MM FXS MINI 20M

English

CAD Files

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_2-2061980-0_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-2061980-0_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-2061980-0_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[FullAXS Brochure \(English\)](#)

English

Product Specifications

[Product Specification](#)

English

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English