

Notes:


- 1) Each cable assembly to be individually bagged.
- 2) 50μ " Gold plating on contacts
- *3) Cable Construction:*

В

Α

- 24 AWG Stranded
- 4Pr, U/UTP, Type CM
- PVC Jacket
- 4) 100% Transmission Tested for Performance

P/N Key:



L	Со	loi	_
	Ε	=	- Blue
	G	=	Grey


XXX	Feet
001	1
003	3
005	5
007	7
010	10
015	15
025	25

Length

Wiring Map: 568B Standard

-#8 Contact Both Ends

#1 Contact




Example Parts Numbers

Feet					
P/N	Color	Length			
BM-6UG001F	Grey	1'			
BM-6UE010F	Blue	10'			

For Part Numbers Not Shown Follow Part Number Key Format

2



DO NOT SCALE DRAWING

DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE

DIMENSIONS: INCHES [METRIC]



206 Van Vorst Street Jersey City, NJ 07302 +1 201 432 0463 http://www.belfuse.com

Bel Patchcord Assembly, C6 U/UTP, 24 awa Component Compliant

THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF BEL FUSE, INC. AND SHALL NOT BE REPRODUCED,
COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN CONSENT OF BEL FUSE, INC.

DRN BY:		DATE 02		
APPD BY:	ET	DATE 02	/22	/19
DWG NO.	CT9991	83	REV.	A2

RoHS

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ±.005 [0.13] ANGLES ARE ± 1 SHEET NO. 1 OF

AutoCAD