## **SIEMENS**

Data sheet 6XV1870-3QN10

## product type designation

product description



## IE TP Cord RJ45/RJ45, 4x2

Patch cable, preferred length, preassembled with two RJ45 connectors (10/100/1000/10000MB)

Industrial Ethernet TP Cord RJ45/RJ45, CAT 6A, TP cable 4x2, preassembled with 2 RJ45 connectors, length 10 m.

suitability for use	Easy connection of terminal devices to the IE FC cabling system
cable designation	LI 02YSCH 4x2x0,15 PIMF GN FRNC
wire length	10 m
electrical data	
number of electrical connections	2
attenuation factor per length	
• at 10 MHz / maximum	0.086 dB/m
• at 100 MHz / maximum	0.28 dB/m
• at 300 MHz / maximum	0.501 dB/m
at 600 MHz / maximum	0.735 dB/m
impedance	
• at 1 MHz 100 MHz	100 Ω
● at 10 MHz 600 MHz	100 Ω
relative symmetrical tolerance	
<ul> <li>of the characteristic impedance at 1 MHz 100 MHz</li> </ul>	15 %
<ul> <li>of the characteristic impedance at 10 MHz 600 MHz</li> </ul>	10 %
transfer impedance per length / at 10 MHz	10 mΩ/m
loop resistance per length / maximum	290 mΩ/m
operating voltage	
RMS value	80 V
NVP value in percent	80 %
mechanical data	
number of electrical cores	8
design of the shield	Overlapped aluminum-clad foil, sheathed in a braided screen of tin- plated copper wires
core diameter	
<ul> <li>of AWG26 insulated conductor</li> </ul>	0.5 mm
outer diameter	
• of inner conductor	0.5 mm
<ul> <li>of the wire insulation</li> </ul>	1 mm
of cable sheath	6.2 mm
symmetrical tolerance of the outer diameter / of cable sheath	0.3 mm
material	
• of the wire insulation	polyethylene (PE)

of cable sheath	FRNC
color	
<ul> <li>of the insulation of data wires</li> </ul>	white/blue, white/orange, white/green, white/brown
<ul> <li>of cable sheath</li> </ul>	green
bending radius	
<ul> <li>with single bend / minimum permissible</li> </ul>	31 mm
<ul> <li>with multiple bends / minimum permissible</li> </ul>	43.5 mm
weight per length	50 kg/km
ambient conditions	
ambient temperature	
during operation	-25 +80 °C
during storage	-25 +80 °C
during transport	-25 +80 °C
during installation	-25 +80 °C
• note	In fixed installation -40 °C to 80 °C
fire behavior	flame resistant according to IEC 60332-1-2, smoke density according to IEC 61034
class of burning behaviour / according to EN 13501-6	Eca
chemical resistance	
to mineral oil	oil resistant according to IEC 60811-2-1 (4 h / 70°C)
• to grease	Conditional resistance
radiological resistance / to UV radiation	not resistant
protection class IP	IP20
product features, product functions, product components	-
product features, product ranctions, product components	, general
•	Yes
<ul><li>halogen-free</li><li>silicon-free</li></ul>	Yes
	1 65
standards, specifications, approvals	No
UL/ETL listing / 300 V Rating	No Var. 5400000 AWW 077/1 5 04070
UL/ETL style / 600 V Rating	Yes; E130266 AWM STYLE 21279
certificate of suitability	Von
EAC approval	Yes
UL approval  Del 10 approval	Yes
RoHS conformity	Yes
standard for structured cabling	Cat6A
Marine classification association	NI-
American Bureau of Shipping Europe Ltd. (ABS)	No
French marine classification society (BV)      All All All All All All All All Al	No
Det Norske Veritas (DNV)	No
Germanische Lloyd (GL)	No
Lloyds Register of Shipping (LRS)  Nime of Kerili (Auto)	No No
Nippon Kaiji Kyokai (NK)     Nippon Kaiji Kyokai (NK)	No
Polski Rejestr Statkow (PRS)	No
reference code	WO
according to IEC 81346-2	WG
• according to IEC 81346-2:2019	WGB
further information / internet-Links	
Internet-Link	
<ul> <li>to web page: selection aid TIA Selection Tool</li> </ul>	http://www.siemens.com/tia-selection-tool
<ul> <li>to website: Industrial communication</li> </ul>	http://www.siemens.com/simatic-net
• to website: Industry Mall	https://mall.industry.siemens.com
<ul> <li>to website: Information and Download Center</li> </ul>	http://www.siemens.com/industry/infocenter
<ul> <li>to website: Selection guide for cables and connectors</li> </ul>	https://sie.ag/2QdlxcP
<ul> <li>to website: Image database</li> </ul>	http://automation.siemens.com/bilddb
• to website: CAx-Download-Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com
last modified:	6/25/2022 🖸