



Product: <u>9445</u>

Electronic, 5 C #20 Str TC, PVC Ins, PVC Jkt, CMG

😭 Request Sample

Product Description

Electronic, 5 Conductor 20AWG (7x28) Tinned Copper, PVC Insulation, PVC Outer Jacket, CMG

Technical Specifications

Product Overview

Suitable Appli									
	cations:	low voltage	e analog signa	als (4-20ma, 0-10v,); low vol	tage control (24v,);	line level audio; \	voice communicat	tions; panel w
onstructi	on Details								
Conductor Element	Number of Element	Size	Chronding	Material					
Conductor(s)		20 AWG	Stranding 7x28	TC - Tinned Coppe	er				
.,									
Element	Material	Nor	. Thickness	Nom. Insulation	Diamotor	Color Cod			
	PVC - Polyvinyl Chlor					Black, White, Red, G			
.,			(******)		,				
Outer Jacket									
Mater	ial Nom. Th yl Chloride 0.032 in (l		Nom. Diam						
)					
Overall Cable	Diameter (Nominal):	0.239 IN (6	.07 mm)						
Electrical (Characteristics								
lectricals									
Element	Nom. Conductor DC	R Nom.	Capacitance	Cond-to-Cond	Ма	x. Current			
Conductor(s)	10.7 Ohm/1000ft	27 pF/	ft (89 pF/m)	3	.2 Amps pe	r Conductor at 25°C			
/oltage									
-	oltage Rating								
	300 V (UL AWM 2464	+)							
Mechanica	I Characteristic	S							
Mechanica Femperature	I Characteristic	S							
emperature		S							
⁻ emperature UL Temperat		S							
	ure Operating	S							
emperature UL Temperat 80°C Bend Radius	ure Operating -20°C to +80°C	s							
emperature UL Temperat 80°C Send Radius Stationary M	ure Operating -20°C to +80°C	S							
^r emperature UL Temperat 80°C	ure Operating -20°C to +80°C in. Installation Min.) 2.4 in (61 mm)	S 63 lbs (29	kg)						

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMG
AWM Compliance:	AWM 2464
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision: Rev

Revision Number: 0.506 Revision Date: 01-20-2023

Part Numbers

Variants

ltem #	Color	UPC
9445 060100	Chrome	612825252481
9445 0601000	Chrome	612825252498
9445 060500	Chrome	612825252504
9445 0605000	Chrome	612825252511
9445 060U1000	Chrome	612825252467

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulators based on their individual usage of the product.