


ULTRAFST RECOVERY RECTIFIERS
Reverse Voltage - 600 V
Forward Current - 20 A

FEATURES

- ◆High speed switching capability
- ◆High current capability
- ◆High forward surge capability
- ◆Low power losses, High efficiency
- ◆For use in low voltage, high frequency inverters
- ◆Lead free in comply with EU RoHS 2011/65/EU directives

MECHANICAL DATA

- ◆Case: TO-220AB/CT TO-220F/FCT TO-263/DC
- ◆Solder bath temperature 275°C maximum, 10s per JESD22-106


Primary Characteristic

| | |
|--------------------------|--------------|
| I_o | 2*10A |
| V_{RRM} | 600V |
| I_{FSM} | 100A |
| V_F | 1.1V |
| T_J Max | 150°C |

Maximum Ratings (Per Leg) at Ta=25°C unless otherwise specified

| Parameter | Symbols | Value | Units |
|----------------------------------------------------------------------|----------------------------------------|------------|-------------|
| Maximum Repetitive Peak Reverse Voltage | V_{RRM} | 600 | V |
| Maximum RMS voltage | V_{RMS} | 600 | V |
| Maximum DC Blocking Voltage | V_{DC} | 600 | V |
| Maximum Average Forward Rectified Current | Per Leg | 10 | A |
| | Total | 20 | |
| Peak Forward Surge Current, 8.3ms Single Half Sine-wave | I_{FSM} | 100 | A |
| Operating Temperature Range | T_J | 150 | °C |
| Storage Temperature Range | T_{STG} | -40 ~ +150 | °C |
| Typical Thermal Resistance (Note1) TO-220AB/CT TO-220F/FCT TO-263/DC | R_{θJA} R_{θJC} | 2/4 | °C/W |

Note1: Thermal resistance from Junction to case per leg mounted on heatsink.
Electrical Characteristics (Per Leg) unless otherwise specified

| Characteristics | Symbols | Value | | Units | |
|------------------------------------------------------------------|-----------------------|----------|------|-----------|-----------|
| | | Typ | Max | | |
| Forward Voltage Drop(Note2) at IF=3A at IF=5A at IF=10A | V_F | TA=25°C | 1.05 | - | V |
| | | TA=125°C | 0.84 | - | |
| | | TA=25°C | 1.15 | - | |
| | | TA=125°C | 0.93 | - | |
| | | TA=25°C | 1.27 | 1.59 | |
| | | TA=125°C | 1.10 | - | |
| Maximum Reverse Current at V _R =600V | I_R | TA=25°C | 0.05 | 1 | uA |
| | | TA=25°C | 2 | - | uA |
| Maximum Reverse Recovery Time at IF=0.5A, IR=1A, IRR=0.25A | T_{RR} | - | 35 | nS | |

Note2: Pulse test: 300 μs pulse width, 1 % duty cycle

RATINGS AND CHARACTERISTIC CURVES

FIG.1 MAXIMUM FORWARD CURRENT DERATING CURVE




FIG. 2 MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT PER LEG




FIG. 3 TYPICAL FORWARD CHARACTERISTICS PER LEG







FIG. 4 TYPICAL REVERSE CHARACTERISTICS PER LEG



Marking on the body




Ordering information

| Part Number | Package | Unit Weight | Base Quantity | Delivery mode |
|-------------|----------|---------------|----------------|----------------------------|
| MUR2060CT | TO-220AB | 0.07oz(1.96g) | 50 pcs / tube | 1000pcs/box 5000pcs/carton |
| MUR2060FCT | TO-220F | 0.06oz(1.74g) | 50 pcs / tube | 1000pcs/box 5000pcs/carton |
| MUR2060DC | TO-263 | 0.04oz(1.16g) | 50 pcs / tube | 1000pcs/box 5000pcs/carton |
| MUR2060DC-R | O-263 | 0.04oz(1.16g) | 800 pcs / reel | 800pcs/box4000pcs/carton |


Note: For Halogen Free molding compound, add "H" suffix to part number above.

Package Outline Dimensions millimeters

TO-220AB



TO-220F



TO-263

